



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



V48M28T15EE 15 Kva 3PH 480V TP-1 Delta Transformer

Eaton Corp

Catalog Number	V48M28T15EE
Manufacturer	Eaton Corp
Description	Eaton General Purpose Ventilated Transformer, DT-3 (3-Phase), PV 480V, Taps: 2 At +2.5% /4 At -2.5%, SV 208Y/120V, 150°C Rise W/ 200°C Insulation System, 15 Kva, Ee
Weight per unit	310.0 (lbs/each)
Product Category	Three Phase Energy Efficient D

Features

dimensions	16.5000 IN X 23.0000 IN X 32.0200 IN
Number of Phases	Three-phase
Primary Voltage	480 V
Secondary Voltage	208 Y/120 V
Tap Size	2 at +2.5% FCAN, 4 at -2.5% FCBN

Descriptions

Description	15 KVA 3PH 480V TP-1 DELTA TRANSFORMER
extra long description	ETN V48M28T15EE Eaton General purpo
Features	Eaton types DS-3 (single-phase) and DT-3 (three-phase) general purpose ventilated dry-type transformers are two-winding, self-cooled, and available in a wide variety of primary and secondary voltage combinations. General purpose transformers are designed for continuous operation at rated kVA. They are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards.
Long Description	Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 15 kVA, EE
Product Type	Eaton General Purpose Ventilated Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680019333
Manufacturers Part Number	V48M28T15EE
UPC	786680019333

Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Ventilated transformer

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	310

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Safety and Security Systems
Frequency Rating	60 Hz
standard	UL Listed, NEMA TP-1 Compliant
Temperature Rating	150 °C rise