



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## VM3P170 VM3 HSG 175W MHP Quad *Hubbell--Killark*

Catalog Number	VM3P170
Manufacturer	Hubbell--Killark
Description	VM3 Series - 175W Metal Halide Quadri-Volt Housing
Weight per unit	28.0 (lbs/each)
Product Category	Lighting Accessories

### Features

amperage rating	Starting amps: 0.95/0.55/0.45/0.40; operating amps: 1.80/1.05/0.90/0.80.
Ballast Type	Constant wattage autotransformer
Lamp Type	M-137 pulse start metal halide
Light Source	Metal Halide Pulse
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number of Lamps	0
Power Factor	0.9
Power Rating	175W
Socket Type	Mogul base, 4KV pulse rated (1500W/600V)
Voltage Rating	Quad - 120/277/347/480 VAC

### Material, Color, and Finish

Color	Tan
fixture material	Copper-free aluminum (less than 4/10 of 1%)
Style	Pulse start metal halide fixture

### Dimensions and Weight

Size	13.45" H x 13.67" W x 13.67" D
------	--------------------------------

### Descriptions

Description	VM3 HSG 175W MHP QUAD
extra long description	KLRK VM3P170 VM3 HSG 175W MHP QUAD
Long Description	VM3 Series - 175W Metal Halide Quadri-Volt Housing
Product Type	VM3 HSG 175W MHP Quad
Special Features	The VM3 Series is a low bay and high bay HID luminaire. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	KILLARK
GTIN	00783936966212
Manufacturers Part Number	VM3P170
series	VM3
UPC	783936966212

## Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
Type	Aluminum pulse start metal halide fixture

## Packaging

Carton	1
Weight Per each	28

## Uses, Certifications, and Standards

Application	Killark CERTILITE V Series sets a new standard for industrial grade HID luminaires. Designed for installations where moisture, dirt, dust, corrosion, and vibration may be present; these fixtures are suitable for NEMA 3 and 4X areas where wind, water, snow
environmental conditions	Hazardous and wet locations
Frequency Rating	60
standard	cULus, cCSAus