



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VR1034 100A 3W4P P&S Recept *Hubbell--Killark*

| | |
|------------------|--------------------------------------------------|
| Catalog Number | VR1034 |
| Manufacturer | Hubbell--Killark |
| Description | 100A 3 Pole 4 Wire Receptacle Assembly - At Type |
| Weight per unit | 3.5 (lbs/each) |
| Product Category | Wiring Devices |

Features

| | |
|-----------------|--------------------------------------------|
| amperage rating | 100 |
| Number of Wires | 3 |
| Voltage Rating | 250;600 |
| Wire Size | extra flex: #4-#2;Regular stranding: #4-#2 |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | 5.37 in x 4.25 in x 4.75 in |
|------|-----------------------------|

Descriptions

| | |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 100A 3W4P P&S RECPT |
| extra long description | KLRK VR1034 100A 3W4P RECEPT ASSY. |
| Long Description | 100A 3 Pole 4 Wire Receptacle Assembly - AT Type |
| Product Type | 100A 3W4P Recept Assy. At |
| Special Features | VersaMate® metallic pin & sleeve plugs, receptacles, and in-line connectors are designed for heavy duty industrial use. These devices supply power to both fixed and portable electrical equipment including pumps, generators, welders, vacuums, blowers and similar apparatus. Suitable for indoor and outdoor use, as well as applications that include wet, cold, hosedown, hazardous and corrosive environments. Configurations are also available in reverse-service and polarized orientations. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | KILLARK |
| GTIN | 00783936078656 |
| Manufacturers Part Number | VR1034 |
| series | VersaMate |
| UPC | 783936078656 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Pin & Sleeve Devices |
| Type | Pin & Sleeve |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 7 |
| Weight Per each | 3.48 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Re?neries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities |
| standard | UL, CSA |