



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WACDC7SPL Accessory Dimmer, (B, BK, Gy)

Eaton Wiring Devices

Catalog Number	WACDC7SPL
Manufacturer	Eaton Wiring Devices
Description	Eaton Wi-Fi Smart Dimmer, Flush, 120V, Back and Side Wire, Black, Brown, and Gray, Single-Pole, Three-Way, 32°F to 104°F (0°C to 40°C), Single-Phase, Multi-Location, PC/PBT, WFD30, Wifi
Weight per unit	0.3700 (lbs/each)
Product Category	Wiring Devices

Features

dimensions	2.3600 IN X 3.7700 IN X 7.4300 IN
Phase	Single-phase
Voltage Rating	120 V

Descriptions

Description	ACCESSORY DIMMER, (B, BK, GY)
extra long description	EWD WACD-C7-SP-L Accessory Dimmer,
Features	Wi-fi smart switches, receptacles, and dimmers from Eaton set up quickly and easily with Amazon's Alexa app--no other hubs or controllers are necessary. Plus Frustration Free Setup starts the connection automatically. Schedule lights to go on and off--and even dim--to fit your daily routine. Save energy and feel more comfortable and secure. You can even add voice-control using an Amazon Echo device.
Long Description	Eaton Wi-Fi smart dimmer, Flush, 120V, Back and side wire, Black, Brown, and Gray, Single-pole, Three-way, 32°F to 104°F (0°C to 40°C), Single-phase, Multi-location, PC/PBT, WFD30, WiFi
Product Type	Accessory Dimmer, (B, BK, Gy)

Manufacturer Information

Brand	Eaton
GTIN	00786689366711
Manufacturers Part Number	WACD-C7-SP-L
UPC	786689366711

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Accessory

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	32
Weight Per each	0.37

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Operating Temperature standard	32 to 104 °F (0 to 40 °C) cULus Listed