



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WFSW15C7SPL Wi-Fi Smart Switch, (B, BK, Gy)

*Eaton Wiring Devices*

Catalog Number	WFSW15C7SPL
Manufacturer	Eaton Wiring Devices
Description	Eaton Wi-Fi Smart Decorator Switch, Black, Grown, and Gray, 60 HZ, Led, CFL, Incandescent, MLV, Elv, Fluorescent, and Halogen, Three-Way, Single-Pole, Multi-Location, Wifi
Weight per unit	0.3300 (lbs/each)
Product Category	Wiring Devices

### Features

amperage rating	15 A
dimensions	2.3600 IN X 3.7700 IN X 7.4300 IN
Voltage Rating	120 V

### Descriptions

Description	WI-FI SMART SWITCH, (B, BK, GY)
extra long description	EWD WFSW15-C7-SP-L Wi-Fi Smart Swit
Features	Wi-fi smart switches, receptacles, and dimmers from Eaton set up quickly and easily with Amazon's Alexa app—no other hubs or controllers are necessary. Plus Frustration Free Setup starts the connection automatically. Schedule lights to go on and off—and even dim—to fit your daily routine. Save energy and feel more comfortable and secure. You can even add voice-control using an Amazon Echo device.
Long Description	Eaton Wi-Fi Smart decorator switch, Black, Grown, and Gray, 60 Hz, LED, CFL, incandescent, MLV, ELV, fluorescent, and halogen, Three-way, Single-pole, multi-location, WiFi
Product Type	Wi-Fi Smart Switch, (B, BK, Gy)

### Manufacturer Information

Brand	Eaton
GTIN	00786689366773
Manufacturers Part Number	WFSW15-C7-SP-L
UPC	786689366773

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Decorator Switch

### Packaging

Carton	1
Package	32
Weight Per each	0.33



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

Frequency Rating

60 Hz

standard

cULus Listed,NOM,FCC Compliant