



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **WF8SWW590CRIMWM6 8" 20W Led Wafer 27K/3K/35K/4K/5K WHT 120V** *Lithonia Lighting*

Catalog Number	WF8SWW590CRIMWM6
Manufacturer	Lithonia Lighting
Description	The Wafer Led Downlights With Switchable White Technology Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment, While Eliminating The Need For Recessed Housings.
Weight per unit	2.3 (lbs/each)
Product Category	Lighting

### **Features**

average life	50,000
dimensions	1600 LM
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1600 LM
Material	Aluminum
media	Yes
Shape	Round
Voltage Rating	120
Warranty	3
Wattage	19.1

### **Material, Color, and Finish**

Color	White
color temperature	2700 ,3000 ,3500 ,4000 ,5000 ,Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate

### **Dimensions and Weight**

Height	1.1
Length	8.9
Width	8.9



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	Canless,New Construction,Remodel
Description	8" 20W LED WAFER 27K/3K/35K/4K/5K WHT 120V
extra long description	LITH WF8 SWW5 90CRI MW M6 8IN wafer
Long Description	The Wafer LED Downlights with Switchable White technology provides high-quality light output and efficiency and features a switch for easy color temperature adjustment, while eliminating the need for recessed housings.
Product Type	Trim

## Manufacturer Information

Brand	JUNO
GTIN	00194994243915
Manufacturers Part Number	WF8 SWW5 90CRI MW M6
UPC	194994243915

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

## Trade Size

aperture size	8 IN
---------------	------

## Packaging

Carton	1
Package	6
Weight Per each	2.3

## Uses, Certifications, and Standards

Application	Education,Healthcare,Hospitality,House of Worship,Residential,Retail,Sports and Recreation
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSACA Title 24,ENERGY STAR,JA8