



## SINGLE GANG DEEP EXTRA HEAVY-DUTY WHILE-IN-USE COVER, GRAY

WIUCED10GL | [Pass & Seymour](#)

### FEATURES & BENEFITS

Extra Heavy-Duty While-In-Use Weatherproof Cover 1 Gang Deep, Gray



- Comply with NEC 2014 Section 406.9 (B)(1) for wet location covers, and conforms to NEMA 3R.
- Listed and identified as “Extra Duty”.
- Covers are self closing as required by UL514C42.3.
- Covers mount vertically and horizontally.
- Body, cover, and plates are made of robust polycarbonate for added durability.
- Mounting screws made of 302 stainless steel for corrosion resistance.
- Single receptacle plate available in 1.405 inch and 1.595 inch openings.
- Deep model available for 20A locking plugs.
- Shallow covers accommodate up to 14/3 AWG extension cords.
- New trigger latch opens easily with one finger.

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Type: While-in-use Covers  
Special Features: Weatherproof

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No

UL Listing No: No  
UN SPSC: 39121305  
UR: No

#### **DIMENSIONS**

Depth (US): 5.00"  
Height (US): 7.40"  
Width (US): 5.34"

#### **TECHNICAL INFORMATION**

Material: Plastic  
Capacity: 1-gang

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant





## SINGLE GANG DEEP EXTRA HEAVY-DUTY WHILE-IN-USE COVER, GRAY

WIUCED10GL | [Pass & Seymour](#)

### FEATURES & BENEFITS

Extra Heavy-Duty While-In-Use Weatherproof Cover 1 Gang Deep, Gray



- Comply with NEC 2014 Section 406.9 (B)(1) for wet location covers, and conforms to NEMA 3R.
- Listed and identified as “Extra Duty”.
- Covers are self closing as required by UL514C42.3.
- Covers mount vertically and horizontally.
- Body, cover, and plates are made of robust polycarbonate for added durability.
- Mounting screws made of 302 stainless steel for corrosion resistance.
- Single receptacle plate available in 1.405 inch and 1.595 inch openings.
- Deep model available for 20A locking plugs.
- Shallow covers accommodate up to 14/3 AWG extension cords.
- New trigger latch opens easily with one finger.

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Type: While-in-use Covers  
Special Features: Weatherproof

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No

UL Listing No: No  
UN SPSC: 39121305  
UR: No

#### **DIMENSIONS**

Depth (US): 5.00"  
Height (US): 7.40"  
Width (US): 5.34"

#### **TECHNICAL INFORMATION**

Material: Plastic  
Capacity: 1-gang

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

