

Wall Light

64 Watt LED

Classic Series LED
TRADITIONAL HID REPLACEMENT

Glare Free



Design is Protected by U.S. Patent No. 9,482,395



WLD64LED

WATTS: 64

CCT: 4500K
LUMENS: 6,966
LPW: 111 CRI: 83
DIMMING: 10-100%

CCT: 3000K
LUMENS: 6,501
LPW: 104 CRI: 81
DIMMING: 10-100%

Ordering Information

CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLD64LED	64W LED Wall Light	120-277	4500K
WLD64LED3K	64W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol
EB	Emergency Back-Up
4	480V Driver


Note: Atlas uses only premium LED compatible photocontrols

Performance


- 95% Efficient Reflector Targets the Light
- Eliminates Glare & Offensive Light
- Less Wasted Light
- More Footcandles on the Ground
- Creates a Smooth & Uniform Light Pattern

Dimensions and Specifications

Overall Height: 9.01" **Depth: 9.78"**
Overall Width: 18.2" **Weight: 15 lbs.**



Recommended Mounting Height - 18-20 ft.



Mtg. Hgt.	FOOTCANDLES ON THE GROUND						Avg. FCs 450 SQ. FT.
	90°			45°			
	5'	10'	15'	5'	10'	15'	
18'	9.6	5.8	4.2	9.5	6.1	3.6	6.5
20'	6.8	4.8	3.4	6.6	5.2	3.4	5.0

200,000+ HOURS



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components



Wall Light

64 Watt LED

Classic Series LED
TRADITIONAL HID REPLACEMENT

Glare Free



Design is Protected by U.S. Patent No. 9,482,395



WLD64LED

WATTS: 64

CCT: 4500K
LUMENS: 6,966
LPW: 111 CRI: 83
DIMMING: 10-100%

CCT: 3000K
LUMENS: 6,501
LPW: 104 CRI: 81
DIMMING: 10-100%

Ordering Information

CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLD64LED	64W LED Wall Light	120-277	4500K
WLD64LED3K	64W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol
EB	Emergency Back-Up
4	480V Driver


Note: Atlas uses only premium LED compatible photocontrols

Performance


- 95% Efficient Reflector Targets the Light
- Eliminates Glare & Offensive Light
- Less Wasted Light
- More Footcandles on the Ground
- Creates a Smooth & Uniform Light Pattern

Dimensions and Specifications

Overall Height: 9.01" **Depth: 9.78"**
Overall Width: 18.2" **Weight: 15 lbs.**



Recommended Mounting Height - 18-20 ft.



200,000+ HOURS



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components

