
WEATHERPROOF TWO GANG BOX, GRAY

WPB332 | [Pass & Seymour](#)



FEATURES & BENEFITS

Weatherproof 2 Gang Box, 3 hole 3/4", 30.5 Cu.In., Gray (1 Hole Each End, 1 Hole in Back)



- Wide range of sizes, depths, and gangs.
- Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.
- 2 closure plugs and mounting lugs furnished with all boxes.
- UL Listed for wet and/or damp locations with appropriate cover.
- Designed for both interior and exterior applications.
- Will accept standard 4 screw mounting covers and single gang weatherproof covers.
- Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.
- Heavy die-cast aluminum.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Size: 2-gang
Type: Box
Special Features: Weatherproof

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No

UL Listing No: Yes
UN SPSC: 39121305
UR: No

DIMENSIONS

Depth (US): 2.24"
Height (US): 4.50"
Width (US): 4.50"

TECHNICAL INFORMATION

Material: Aluminum
Capacity: 2-gang
Feeds: Three quarter inch knockouts

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: INDIA
Buy American Act Status: No

WEATHERPROOF TWO GANG BOX, GRAY

WPB332 | [Pass & Seymour](#)



FEATURES & BENEFITS

Weatherproof 2 Gang Box, 3 hole 3/4", 30.5 Cu.In., Gray (1 Hole Each End, 1 Hole in Back)



- Wide range of sizes, depths, and gangs.
- Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.
- 2 closure plugs and mounting lugs furnished with all boxes.
- UL Listed for wet and/or damp locations with appropriate cover.
- Designed for both interior and exterior applications.
- Will accept standard 4 screw mounting covers and single gang weatherproof covers.
- Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.
- Heavy die-cast aluminum.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Size: 2-gang
Type: Box
Special Features: Weatherproof

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No

UL Listing No: Yes
UN SPSC: 39121305
UR: No

DIMENSIONS

Depth (US): 2.24"
Height (US): 4.50"
Width (US): 4.50"

TECHNICAL INFORMATION

Material: Aluminum
Capacity: 2-gang
Feeds: Three quarter inch knockouts

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: INDIA
Buy American Act Status: No