



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WPX3LED40KMVOLT 69W Led Wall Pack 4K 9200LM 120-277V Dark Bronze *Lithonia Lighting*

Catalog Number	WPX3LED40KMVOLT
Manufacturer	Lithonia Lighting
Description	The WPX Family Of Led Wall Packs Are Your Best Choice For Your Everyday Wall Mounted Lighting Needs. No Longer Will Your Customers Have to Sacrifice Performance and Style to Get The Low Initial Cost That They Demand. With Three Sizes and Lumen Packages Of 1, 550 to 9, 200 Lumens, The WPX Family Is A Site-Wide Solution, Replacing Up to 400W Metal Halide Wall Packs. Since The WPX Footprints Are Larger Than That Of Typical Metal Halide Glass Wall Packs, They Fully Cover Unsightly Stains, Resulting In A Neat App
Weight per unit	8.2 (lbs/each)
Product Category	Lighting

Features

Lamp Included	Yes
Lamp Type	LED - Static
lumens	9200 LM
Material	Aluminum
media	Yes
pallet quantity	96
Power Source	Hardwired
Socket Type	Integrated LED
Voltage Rating	120-277
Wattage	69

Material, Color, and Finish

Color	Bronze
color rendering index (cri)	70
color temperature	4000
Finish	Gloss
fixture material	aluminum
Style	Traditional

Dimensions and Weight

Height	5.5
Length	9.5
Width	13



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	69W LED WALL PACK 4K 9200LM 120-277V DARK BRONZE
extra long description	LITH WPX3 LED 40K MVOLT DDBXD M2 LE
Features	Contractor Select
Long Description	The WPX family of LED wall packs are your best choice for your everyday wall mounted lighting needs. No longer will your customers have to sacrifice performance and style to get the low initial cost that they demand. With three sizes and lumen packages of 1,550 to 9,200 lumens, the WPX family is a site-wide solution, replacing up to 400W metal halide wall packs. Since the WPX footprints are larger than that of typical metal halide glass wall packs, they fully cover unsightly stains, resulting in a neat app
Product Type	Wallpack
Special Features	The WPX family of LED wall packs are your best choice for your everyday wall mounted lighting needs. No longer will your customers have to sacrifice performance and style to get the low initial cost that they demand. With three sizes and lumen packages of 1,550 to 9,200 lumens, the WPX family is a site-wide solution, replacing up to 400W metal halide wall packs. Since the WPX footprints are larger than that of typical metal halide glass wall packs, they fully cover unsightly stains, resulting in a neat app

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193048870794
Manufacturers Part Number	WPX3 LED 40K MVOLT DDBXD M2
UPC	193048870794

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Wallpack

Packaging

Carton	1
Package	2
Weight	11
Weight Per each	8.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Automotive & Parking, Education, Government, House of
Worship, Manufacturing, Offices & Banks, Parking
Garage, Retail, Sports and Recreation, Transportation, Utility,
Closet, Warehouses

environmental conditions

OUTDOOR

Mounting

SURFACE

standard

CSADLC Premium, DLC Standard