



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WW7322 3/4"X66' Red Prem Vny Tape

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | WW7322   |
| Manufacturer     | Nsi Industries   |
| Description      | Warriorwrap WW-732-RD Red Vinyl Professional-Quality Electrical Tape Is Strong Enough For Demanding Environments and Highly Resistant to Abrasion and Corrosion. This Tape Is 7MIL Thick, 66FT Long and Has A Max Temperature Rating Of 220 Degrees F. The Strong Adhesion Helps Stick to Uneven Surfaces and Keeps The Backing In Place. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires. |
| Weight per unit  | 0.2200 (lbs/each)  |
| Product Category | Markers & Marking Tapes  |

### Features

|                   |           |
|-------------------|-----------|
| adhesion strength | 33.2      |
| Material          | Vinyl     |
| maximum voltage   | 600       |
| Temperature Range | 0° - 221° |
| Tensile Strength  | 19.8      |
| Warranty          | 1 YEAR    |

### Material, Color, and Finish

|                  |                                      |
|------------------|--------------------------------------|
| Backing Material | Plasticized Polyvinyl Chloride (PVC) |
| Color            | Red                                  |

### Dimensions and Weight

|           |  |
|-----------|--|
| Length    | 66   |
| Size      | Thickness - 7mil - Length-66' - Width 3/4" |
| Thickness | .007                                       |
| Width     | .750                                       |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 3/4"X66' RED PREM VNY TAPE   |
| extra long description | NSI WW-732-RD Vyl Elec Tape Premium  |
| Features               | Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity to hold tight in residential or commercial en |
| Long Description       | WarriorWrap WW-732-RD Red Vinyl Professional-Quality Electrical Tape is strong enough for demanding environments and highly resistant to abrasion and corrosion. This tape is 7mil thick, 66ft long and has a max temperature rating of 220 degrees F. The strong adhesion helps stick to uneven surfaces and keeps the backing in place. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.   |
| Product Type           | Vyl Elec Tape Premium 7MIL .75" 60FT RD  |
| Special Features       | Superior Adhesion and Elasticity, Extreme Weather Performance, Excellent Tensile Strength, Highly Resistant to UV, Abrasion and Corrosion.   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381367181 |
| Manufacturers Part Number | WW-732-RD      |
| UPC                       | 662381367181   |

## Taxonomies, Classifications, and Categories

|                      |         |
|----------------------|---------|
| Category Description | TAPE    |
| Type                 | Premium |

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 100  |
| Weight Per each | 0.22 |

## Uses, Certifications, and Standards

|             |        |
|-------------|--------|
| Application | NSI    |
| standard    | UL 510 |