



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353



WWCGRB Green Winged Connector

Nsi Industries

| | |
|------------------|--|
| Catalog Number | WWCGRB |
| Manufacturer | Nsi Industries |
| Description | Winged Wire Connector, (2) #14 Awg Conductor Size, (5) #12 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Green Insulation Color, +221 °F Operating Temperature, 0.795 In Overall Width, 1.134 In Overall Height, 600 V, 3.15 LB |
| Weight per unit | 0.0060 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------------|---------------|
| Material | Thermoplastic |
| Number of Conductors | 1 |
| Voltage Rating | 600 |
| Warranty | 1 YEAR |
| Wire Type | CU Wire Only |

Material, Color, and Finish

| | |
|--------|---------------|
| Color | Green |
| Finish | Thermoplastic |

Dimensions and Weight

| | |
|------|---------------------------|
| Size | H=1.13 - W=.795 - ID=.327 |
|------|---------------------------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | GREEN WINGED CONNECTOR |
| extra long description | NSI WWC-GR-B Easy-Twist Winged Tan |

Manufacturer Information

| | |
|---------------------------|----------------|
| GTIN | 00662381141286 |
| Manufacturers Part Number | WWC-GR-B |
| UPC | 662381141286 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | WIRE NUTS |
| Type | Winged Wire Connectors |

Availability

| | |
|-------------|-----|
| minimum qty | 500 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 500 |
| Weight Per each | 0.006 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353

Uses, Certifications, and Standards

| | |
|--------------------------|----------------|
| Application | Grounding Wire |
| environmental conditions | 105 C |
| standard | UL 467 |
| Temperature Rating | 105 C |