



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WT51SK Wingtwist Wire Conn, WT51 Yellow, 25, 000/Barrel *Ideal*

Catalog Number	WT51SK
Manufacturer	Ideal
Description	Buchanan, Wire Connector, Wingtwist, Conductor Range: 18 - 10 Awg, 2/18 Awg Min, 3/12 Awg Max, Number Of Conductors: 1 to 6, Material: Flame-Retardant Polypropylene, Color: Yellow, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT51
Weight per unit	110.0 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-Retardant Polypropylene
Number of Conductors	1 to 6
Voltage Rating	600

### Material, Color, and Finish

Color	Yellow
-------	--------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	WINGTWIST WIRE CONN, WT51 YELLOW, 25,000/BARREL
extra long description	IDEAL WT51-SK WINGTWIST WT51 YLW, 2
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value. The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections. With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric protection.
Long Description	Buchanan, Wire Connector, WingTwist, Conductor Range: 18 - 10 AWG, 2/18 AWG Min, 3/12 AWG MAX, Number Of Conductors: 1 to 6, Material: Flame-retardant Polypropylene, Color: Yellow, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT51
Product Type	Wingtwist WT51 Ylw, 25K Drum
Special Features	Features: Five Color-Coded Models Cover Common Construction Wire Ranges; Green Model Designed For Ground Connections; Unique Contoured Wing Design Acts As Built-In Wrench Providing Maximum Torque With Minimum Effort; Fixed, Square-Wire Spring Threads Itself Creating Secure Pressure Grip; Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection; UL 486C Listed (WGR UL 467 Listed) And CSA C22.2 #188 Certified; 1,000V Maximum In Fixtures And Signs; Model

## Manufacturer Information

Brand	Buchanan
GTIN	00781789624143
Manufacturers Part Number	WT51-SK
sub brand	WingTwist
UPC	781789624143

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

## Packaging

Carton	25000
Weight Per each	110



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS