



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WW716WT 3/4"X60' WHT GP Vny Tape

Nsi Industries

Catalog Number

WW716WT

Manufacturer

Nsi Industries

Description

Warriorwrap WW-716-WT White Vinyl General Use Electrical Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 7MIL Thick, 60FT Long and Has A Max Temperature Rating Of 176 Degrees. The Strong Adhesion Helps Stick to Uneven Surfaces and Keeps The Backing In Place. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires.

Weight per unit

0.1900 (lbs/each)

Product Category

Markers & Marking Tapes

Features

adhesion strength

16

Material

Vinyl

maximum voltage

600

Temperature Range

20° - 176°

Tensile Strength

15

Warranty

1 YEAR

Material, Color, and Finish

Backing Material

Plasticized Polyvinyl Chloride (PVC)

Color

White

Dimensions and Weight

Length

60

Size

Thickness - 7mil - Length-60' - Width 3/4"

Thickness

.007

Width

.75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/4"X60' WHT GP VNY TAPE
extra long description	NSI WW-716-WT Vinyl Electrical Tape
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity to hold tight in indoor residential or commer
Long Description	WarriorWrap WW-716-WT White Vinyl General Use Electrical Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 7mil thick, 60ft long and has a max temperature rating of 176 degrees. The strong adhesion helps stick to uneven surfaces and keeps the backing in place. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.
Product Type	Vinyl Electrical Tape 7MIL .75" 60FT WT
Special Features	Good Ahesion and Elasticity, All Weather Performance, Great Tensile Strength, Resistant Tto UV, Abrasion and Corrosion, Falme-Retardant.

Manufacturer Information

Brand	NSI
GTIN	00662381367457
Manufacturers Part Number	WW-716-WT
UPC	662381367457

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	GENERAL PURPOSE

Packaging

Carton	1
Weight Per each	0.19

Uses, Certifications, and Standards

Application	NSI
standard	UL 510