



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWCGB Gry Winged Wire Conn

Nsi Industries

Catalog Number	WWCGB
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-G-B 250-Count Bag Of Grey Winged Wire Connectors Are Designed For Use On Copper Wires In The 18-8 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You
Weight per unit	2.8 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600
Warranty	1 YEAR
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Gray
Finish	Thermoplastic

Dimensions and Weight

Size	H=1.31 - W=1.00 - ID=.394
------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	GRY WINGED WIRE CONN
extra long description	NSI WWC-G-B Easy-Twist Winged Red -
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in
Long Description	The Easy-Twist WWC-G-B 250-Count Bag of Grey Winged Wire Connectors are designed for use on copper wires in the 18-8 AWG size range. They are made of flame-retardant thermoplastic rated for a maximum temperature of 105°C (221°F). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you
Product Type	Easy-Twist Winged Red - STD Jar
Special Features	Winged Grey Wire Connector - 100 Pcs Bag

Manufacturer Information

Brand	NSI
GTIN	00662381141408
Manufacturers Part Number	WWC-G-B
UPC	662381141408

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Winged Wire Connectors

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per each	2.8

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C
Temperature Rating	105 C