




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2001 ATKINSON DRIVE
75901-0000, TX Lufkin
Phone: 936-632-9733
Fax: 936-632-9736



WWSR10 High Voltage Silicone Rubber 30 FT X 1 In

Nsi Industries

| | |
|------------------|---|
| Catalog Number | WWSR10 |
| Manufacturer | Nsi Industries |
| Description | Warriorwrap WW-SR-10 Gray Silicone Rubber High-Voltage Splicing Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 20MIL Thick, 1 Inch Wide, 30FT Long and Is Made From Silicone Rubber. The Self-Bonding Design Features No Adhesive But Forms A Solid Mass When Wrapped Under Tension. Top Breaking Strength, Elongation and Elasticity Make Warriorwrap An Excellent Choice For Heavy-Duty Jobs Including Jacketing High-Voltage Terminations On Extru |
| Weight per unit | 0.1600 (lbs/each) |
| Product Category | Markers & Marking Tapes - Tape |

Features

| | |
|-------------------|-----------------|
| Material | SILICONE RUBBER |
| maximum voltage | 69 |
| Temperature Range | 180 C, 356 F |
| Tensile Strength | 580 |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|------------------|------------|
| Backing Material | NSI |
| Color | Light Grey |

Dimensions and Weight

| | |
|-----------|---------------------|
| Length | 30 |
| Size | L=30 FT - W=1.00 IN |
| Thickness | 20 |
| Width | 1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2001 ATKINSON DRIVE
75901-0000, TX Lufkin
Phone: 936-632-9733
Fax: 936-632-9736

Descriptions

| | |
|------------------------|---|
| Description | HIGH VOLTAGE SILICONE RUBBER 30 FT X 1 IN |
| extra long description | NSI WW-SR-10 Silicone Rubber Tape H |
| Features | Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity. This silicone rubber splicing tape is a self-amalgamating, chemically cross-linked tape that self-bonds when wrapped under tension and forms a solid mass within minutes of applicati |
| Long Description | WarriorWrap WW-SR-10 Gray Silicone Rubber High-Voltage Splicing Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 20mil thick, 1 inch wide, 30ft long and is made from silicone rubber. The self-bonding design features no adhesive but forms a solid mass when wrapped under tension. Top breaking strength, elongation and elasticity make WarriorWrap an excellent choice for heavy-duty jobs including jacketing high-voltage terminations on extru |
| Product Type | Silicone Rubber Tape HV 1" 30FT |
| Special Features | Unique triangular cross-section, Self-amalgamating, UV and Oil resistant, Center line for half-lapping guide |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381365705 |
| Manufacturers Part Number | WW-SR-10 |
| UPC | 662381365705 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------|
| Category Description | TAPE |
| Type | Silicone Rubber |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.16 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | For jacketing of high voltage terminations on extruded dielectric cables through 69000 volts. For insulating high temperature silicone insulated cables. A positive oil stop in the construction of transition splices. |
|-------------|---|