



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

XB3UKF25 Triple 3 Level Feed-Thru TB 24-12awg

Eaton Corp

Catalog Number	XB3UKF25
Manufacturer	Eaton Corp
Description	Eaton XB IEC Terminal Block, Screw Connection Triple Level Sensor/Actuator, IEC 30 A, UI 15 A, Gray, #14 Awg/2.5 MM2 Max Wire, IEC 250 V, UI 300 V, IEC #24-12 Awg, UI #30-14 Awg Wire Range
Weight per unit	0.0400 (lbs/each)
Product Category	Terminal Blocks & Accessories

Features

amperage rating	30A (IEC), 15A (UL)
dimensions	2.8000 IN X 0.2500 IN X 2.1000 IN
Voltage Rating	IEC 250V, UL 300V
Wire Size	#14 AWG/2.5 mm2

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	TRIPLE 3 LEVEL FEED-THRU TB 24-12AWG
extra long description	ETN XB3UKF25 3 LEVEL FEED-THRU TB 2
Features	Eaton's robust line of XB IEC terminal blocks are designed for prolonged life under harsh conditions. This comprehensive portfolio comes complete with universal accessories across three connection technologies – screw, spring cage and insulation displacement connection (IDC) – reducing inventory and logistic costs. With space savings in mind, the terminal blocks are small, adjustable and provide maximum flexibility and easy installation.
Long Description	Eaton XB IEC terminal block, Screw connection triple level sensor/actuator, IEC 30 A, UL 15 A, Gray, #14 AWG/2.5 mm2 max wire, IEC 250 V, UL 300 V, IEC #24-12 AWG, UL #30-14 AWG wire range
Product Type	3 Level Feed-Thru TB 24-12awg

Manufacturer Information

Brand	Eaton Corp
Manufacturers Part Number	XB3UKF25

Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCKS POWER DIST BLOCKS
Type	Terminal Block



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	50
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Other
standard	UL Listed, CSA Certified