

# Eaton XBUT6FBNL24

Catalog Number: XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm<sup>2</sup> maximum wire

## General specifications



|                             |   |
|-----------------------------|---|
| <b>Product Name</b>         | <b>Catalog Number</b>   |
| Eaton XB IEC terminal block | XBUT6FBNL24   |
| <b>UPC</b>                  | <b>Product Length/Depth</b>                                     |
| 782116905263                | 1.85 in   |
| <b>Product Height</b>       | <b>Product Width</b>  |
| 2.17 in                     | 0.32 in   |
| <b>Product Weight</b>       | <b>Warranty</b>   |
| 0.03 lb                     | 1 year  |
| <b>Certifications</b>       | <b>Catalog Notes</b>  |
| UL Listed<br>CSA Certified  | As disconnect terminal block 500V, as fuse terminal block 400V. |

Type

Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse

Amperage Rating

10A (IEC), 10A (UL)

Voltage rating

UL 400V

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT6FBNL24](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XBUT6FBNL24

Catalog Number: XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm<sup>2</sup> maximum wire

## General specifications



|                             |   |
|-----------------------------|---|
| <b>Product Name</b>         | <b>Catalog Number</b>   |
| Eaton XB IEC terminal block | XBUT6FBNL24   |
| <b>UPC</b>                  | <b>Product Length/Depth</b>                                     |
| 782116905263                | 1.85 in   |
| <b>Product Height</b>       | <b>Product Width</b>  |
| 2.17 in                     | 0.32 in   |
| <b>Product Weight</b>       | <b>Warranty</b>   |
| 0.03 lb                     | 1 year  |
| <b>Certifications</b>       | <b>Catalog Notes</b>  |
| UL Listed<br>CSA Certified  | As disconnect terminal block 500V, as fuse terminal block 400V. |

Type

Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse

Amperage Rating

10A (IEC), 10A (UL)

Voltage rating

UL 400V

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT6FBNL24](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)