

# Specifications

## Eaton XBUT6FBNL250

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 110-250V, 0.5-2.5 mA, Black, 8 AWG/6 mm<sup>2</sup> maximum wire



### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT6FBNL250
<b>UPC</b>	782116905287
<b>PRODUCT LENGTH/DEPTH</b>	1.85 in
<b>PRODUCT HEIGHT</b>	2.17 in
<b>PRODUCT WIDTH</b>	0.32 in
<b>PRODUCT WEIGHT</b>	0.05 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	As disconnect terminal block 500V, as fuse terminal block 400V.



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse
<b>AMPERAGE RATING</b>	10A (IEC), 10A (UL)
<b>VOLTAGE RATING</b>	UL 400V

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -  
XBUT6FBNL250](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.



# Specifications

## Eaton XBUT6FBNL250

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 110-250V, 0.5-2.5 mA, Black, 8 AWG/6 mm<sup>2</sup> maximum wire



### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT6FBNL250
<b>UPC</b>	782116905287
<b>PRODUCT LENGTH/DEPTH</b>	1.85 in
<b>PRODUCT HEIGHT</b>	2.17 in
<b>PRODUCT WIDTH</b>	0.32 in
<b>PRODUCT WEIGHT</b>	0.05 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	As disconnect terminal block 500V, as fuse terminal block 400V.



*Powering Business Worldwide*

## Product specifications

<b>TYPE</b>	Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse
<b>AMPERAGE RATING</b>	10A (IEC), 10A (UL)
<b>VOLTAGE RATING</b>	UL 400V

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -  
XBUT6FBNL250](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

