

Eaton XTOE005CCS

Catalog Number: XTOE005CCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 1-5A overload range, 45 mm frame, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications



Photo is representative

Product Name

Eaton C440 electronic overload relay

Catalog Number

XTOE005CCS

UPC

786685416465

Product Length/Depth

1.8 in

Product Height

4.3 in

Product Width

1.42 in

Product Weight

1 lb

Compliances

CE Marked

ATEX Compliant

RoHS Compliant

Certifications

EN 60947

UL Listed

CSA Certified

IEC 60947

defaultTaxonomyAttributeLabel

Overload range

1-5A

Type

Electronic overload relay

Frame size

45 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTOE_C 3D Inventor](#)

[XTOE_C 2D Drawing Xchange](#)

[XTOE_C AutoCAD 2D Footprint](#)

[XTOE_C AutoCAD 2D Footprint \(mm\)](#)

[XTOE_C 3D Model Xchange](#)

[XTOE_C 2D PDF](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE005CCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTOE005CCS

Catalog Number: XTOE005CCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 1-5A overload range, 45 mm frame, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications



Photo is representative

Product Name

Eaton C440 electronic overload relay

Catalog Number

XTOE005CCS

UPC

786685416465

Product Length/Depth

1.8 in

Product Height

4.3 in

Product Width

1.42 in

Product Weight

1 lb

Compliances

CE Marked

ATEX Compliant

RoHS Compliant

Certifications

EN 60947

UL Listed

CSA Certified

IEC 60947

defaultTaxonomyAttributeLabel

Overload range

1-5A

Type

Electronic overload relay

Frame size

45 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTOE_C 3D Inventor](#)

[XTOE_C 2D Drawing Xchange](#)

[XTOE_C AutoCAD 2D Footprint](#)

[XTOE_C AutoCAD 2D Footprint \(mm\)](#)

[XTOE_C 3D Model Xchange](#)

[XTOE_C 2D PDF](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE005CCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)