



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA362N 600 Cu 2H Long Nema *Burndy LLC*

Catalog Number	YA362N
Manufacturer	Burndy LLC
Description	600 Kcmil Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Green Color Code, 22 or 472 Die Index.
Weight per unit	0.8900 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	22
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	GREEN
------------	-------

Descriptions

Description	600 CU 2H LONG NEMA
extra long description	BUR YA362N 600 CU 2-HOLE LONG NEMA
Long Description	600 kcmil CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Green Color Code, 22 or 472 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 2-3/4 IN, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Tongue Angle: Straight, Die Index: 22, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y35, Y39, Y750, PAT750 Tool, U36RT, U32ART Die, (4), Y46 Tool, U36RT, U32ART Die With PUADP-1 Adapter, (4), Color Code: Green, Conductor Type: Commercial Stranded Copper, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81

Manufacturer Information

Brand	BURNDY
GTIN	00781810521526
Manufacturers Part Number	YA362N
UPC	781810521526

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.89

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B