



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA4CL3BOX 4AWG Cop 1H Lug

Burndy LLC

Catalog Number	YA4CL3BOX
Manufacturer	Burndy LLC
Description	4 Awg Cu, One Hole, 5/16 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Gray Color Code, 8 or 346 Die Index.
Weight per unit	0.0004 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	8
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	GRAY
------------	------

### Descriptions

Description	4AWG COP 1H LUG
extra long description	BUR YA4CL3BOX CULUG- 4 STR-SHORT-5/
Long Description	4 AWG CU, One Hole, 5/16 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, GRAY Color Code, 8 or 346 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Package: Box, Die Index: 8, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Wire Strip Length: 7/8 IN, Color Code: Gray, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W4CVT, W4CRT, X4CRT Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W4CVT, W4CRT, X4CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U4CRT, U6CABT Die, (1), Y46 Tool, U4CRT, U6CABT Die

### Manufacturer Information

Brand	BURNDY
GTIN	00781810552438
Manufacturers Part Number	YA4CL3BOX
UPC	781810552438

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.0004

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B