



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA4CTC38 Compression Copper #4 Awg STRD 1 Hole; 3/8" ST *Burndy LLC*

Catalog Number	YA4CTC38
Manufacturer	Burndy LLC
Description	4 Awg Cu, One Hole, 3/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/Csa, 90 C, Up to 35KV, Gray Color Code, 8 or 346 Die Index.
Weight per unit	0.0300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	8
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	GRAY
------------	------

Descriptions

Description	COMPRESSION COPPER #4 AWG STRD 1 HOLE; 3/8" ST
extra long description	BUR YA4CTC38 HYLUG-LONG-4 STR-3/8ST
Long Description	4 AWG CU, One Hole, 3/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV,GRAY Color Code, 8 or 346 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Wire Strip Length: 1-3/16 IN, Color Code: Gray, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W4CVT, W4CRT, X4CRT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W4CVT, W4CRT, X4CRT Die, (2), Y35, Y39, Y750, PAT750 Tool, U4CRT, U6CABT Die, (2), Y46 Tool, U4CRT, U6CABT Die With PUADP-1 Adapter, (2)

Manufacturer Information

Brand	BURNDY
GTIN	00781810270455
Manufacturers Part Number	YA4CTC38
UPC	781810270455

Taxonomies, Classifications, and Categories

Type	Long Barrel, Electro-Tin Plated
------	---------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B