



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA25N 1/0 Cu 1H Long 1/2 Lug *Burndy LLC*

Catalog Number	YA25N
Manufacturer	Burndy LLC
Description	1/0 Awg Cu, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Pink Color Code, 12 or 348 Die Index.
Weight per unit	0.0800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	12
Material	Copper
pallet quantity	18560
Voltage Rating	35

Material, Color, and Finish

Color Code	PINK
------------	------

Descriptions

Description	1/0 CU 1H LONG 1/2 LUG
extra long description	BUR YA25N 1/0 CU 1-HOLE LONG 1/2
Long Description	1/0 AWG CU, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV,PINK Color Code, 12 or 348 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 12, Wire Strip Length: 1-7/16 IN, Finish: Electro-Tin Plated, Tongue Angle: Straight, Temperature Rating: 90 DEG C, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W25VT, W25RT, X25RT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W25VT, W25RT, X25RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U25RT, U2CABT Die, (2), Y46 Tool, U25RT, U2CABT Die With PUADP-1 Adapter, (2), C

Manufacturer Information

Brand	BURNDY
GTIN	00781810018880
Manufacturers Part Number	YA25N
UPC	781810018880

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	40
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B