

BURNDY Catalog Number
UPC Number

YAV26L
7818100256977

Description

2/0 HVYDTY RING 3/8 STUD, Index
No:44

Status

Active

Web Use

BURNDY Product Line

Dimensional

| | |
|----------------|----------|
| Tongue Angle | Straight |
| Strip Length | 13/16 |
| Length (in) | 2.31 |
| Tongue Type | Ring |
| Pad Width (in) | 0.93 |

General

| | |
|---------------------|--|
| Product Description | Copper Compression Lug, 1 Hole w/ Inspection Window, AN-2/0 Flex, 3/8" Stud, Short Barrel, Tin Plated |
|---------------------|--|

Conductor(s)

| | |
|-----------------------------|---------|
| Aircraft Cable Size (Range) | AN 00 |
| Copper Solid Size (Range) | N/A |
| Navy Cable Size (Range) | N/A |
| Copper Stranded (Range) | 2/0 AWG |

Physical

| | |
|--------------------|----------|
| Type of Plating | Tin |
| Connector Type | Terminal |
| Plated (Yes or No) | Y |

Approvals / Certifications

| | |
|---------------------|--------------------------------------|
| UL Listed | Y |
| CSA Certified | Y |
| ROHS Compatible | Compliant |
| UL Recognized | N |
| Mil-Spec Class Code | Class 1 |
| CULUS | N |
| Industry Standards | UL467, Military Specified (Mil-Spec) |

Documentation

For further technical assistance, please contact us


BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175



BURNDY Catalog Number
UPC Number

YAV26L
7818100256977

Description

2/0 HVYDTY RING 3/8 STUD, Index
No:44

Status

Active

Web Use

BURNDY Product Line

Dimensional

| | |
|----------------|----------|
| Tongue Angle | Straight |
| Strip Length | 13/16 |
| Length (in) | 2.31 |
| Tongue Type | Ring |
| Pad Width (in) | 0.93 |

General

| | |
|---------------------|--|
| Product Description | Copper Compression Lug, 1 Hole w/ Inspection Window, AN-2/0 Flex, 3/8" Stud, Short Barrel, Tin Plated |
|---------------------|--|

Conductor(s)

| | |
|-----------------------------|---------|
| Aircraft Cable Size (Range) | AN 00 |
| Copper Solid Size (Range) | N/A |
| Navy Cable Size (Range) | N/A |
| Copper Stranded (Range) | 2/0 AWG |

Physical

| | |
|--------------------|----------|
| Type of Plating | Tin |
| Connector Type | Terminal |
| Plated (Yes or No) | Y |

Approvals / Certifications

| | |
|---------------------|--------------------------------------|
| UL Listed | Y |
| CSA Certified | Y |
| ROHS Compatible | Compliant |
| UL Recognized | N |
| Mil-Spec Class Code | Class 1 |
| CULUS | N |
| Industry Standards | UL467, Military Specified (Mil-Spec) |

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175