



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA28LBOX 4/0 Cu 1H Short 1/2 Burndy LLC

Catalog Number	YA28LBOX
Manufacturer	Burndy LLC
Description	4/0 Awg Cu, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Purple Color Code, 15 Die Index.
Weight per unit	0.1000 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	15
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	PURPLE
------------	--------

### Descriptions

Description	4/0 CU 1H SHORT 1/2
extra long description	BUR YA28LBOX 4/0 CU 1-HOLE SHORT 1/2
Long Description	4/0 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, PURPLE Color Code, 15 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 1-1/8 IN, Finish: Electro-Tin Plated, Package: Box, Temperature Rating: 90 DEG C, Die Index: 15, Tongue Angle: Straight, Color Code: Purple, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W28VT, W28RT, X28RT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W28VT, W28RT Die, (2), X28RT Die, (3), Y35, Y39, Y750, PAT750 Tool, U28RT Die, (1), Y46 Tool, U28RT Die Wi

### Manufacturer Information

Brand	BURNDY
GTIN	00781810554104
Manufacturers Part Number	YA28LBOX
UPC	781810554104

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B