



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA4CL3BOX 4AWG Cop 1H Lug *Burndy LLC*

Catalog Number	YA4CL3BOX
Manufacturer	Burndy LLC
Description	4 Awg Cu, One Hole, 5/16 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Gray Color Code, 8 or 346 Die Index.
Weight per unit	0.0004 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	8
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	GRAY
------------	------

Descriptions

Description	4AWG COP 1H LUG
extra long description	BUR YA4CL3BOX CULUG- 4 STR-SHORT-5/
Long Description	4 AWG CU, One Hole, 5/16 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, GRAY Color Code, 8 or 346 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Package: Box, Die Index: 8, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Wire Strip Length: 7/8 IN, Color Code: Gray, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W4CVT, W4CRT, X4CRT Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W4CVT, W4CRT, X4CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U4CRT, U6CABT Die, (1), Y46 Tool, U4CRT, U6CABT Die

Manufacturer Information

Brand	BURNDY
GTIN	00781810552438
Manufacturers Part Number	YA4CL3BOX
UPC	781810552438

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.0004

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B