



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YGLR29C34 2-250 Ground Grid to 3/4 Ro Burndy LLC

Catalog Number	YGLR29C34
Manufacturer	Burndy LLC
Description	Copper Compression Connector, Ground Rod to Grid, 2 Awg (STR) to 250 Kcmil, 3/4" Ground Rod.
Weight per unit	0.9900 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	997
Material	Copper
pallet quantity	1776

Descriptions

Description	2-250 GROUND GRID TO 3/4 RO
extra long description	BUR YGLR29C34 2-250 GRD GRID TO 3/4
Long Description	Copper Compression Connector, Ground Rod to Grid, 2 AWG (Str) to 250 kcmil, 3/4" Ground Rod.
Product Type	Compression
Special Features	Features: Ground Grid Connector For A Wide Range Of Copper Cable To Ground Rod, Provides High Torque Strength On Ground Rod, UL467 Listed, Acceptable For Direct Burial In Earth And Concrete, Prefilled With PENETROX Compound And Strip Sealed, Ground Rod Size: 3/4 IN, Conductor Size (run - Mm): 35 -120 SQ-MM, Conductor Type: Run: Copperweld, Commercial Stranded Copper, Metric Stranded Cable, Conductor Size (run - Range): Copperweld: 91.65 - 248.8 KCMIL, Code: 2 AWG - 250 KCMIL, Tools, Die Set Catalog Number,

Manufacturer Information

Brand	BURNDY
GTIN	00781810220825
Manufacturers Part Number	YGLR29C34
UPC	781810220825

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Taps

Packaging

Carton	1
Package	6
Weight Per each	0.99



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Direct Burial In Earth And Concrete
standard	UL467;IEEE 837;IEEE 837 2014 Qualified