



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA6CLBOX 6AWG STR Cu 1H Short 1

Burndy LLC

Catalog Number	YA6CLBOX
Manufacturer	Burndy LLC
Description	6 Awg Cu, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Blue Color Code, 7 or 374 Die Index.
Weight per unit	0.0004 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	7
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	BLUE
------------	------

Descriptions

Description	6AWG STR CU 1H SHORT 1
extra long description	BUR YA6CLBOX 6 STR CU 1-HOLE SHORT
Long Description	6 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, BLUE Color Code, 7 or 374 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight, Die Index: 7, Package: Box, Wire Strip Length: 7/16 IN, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W5CVT, W5CRT, X5CRT, X8CART Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W5CVT, W5CRT, X5CRT, X8CART Die, (1), Y35, Y39, Y750, PAT750 Tool, U5CRT Die, (1), Y46 Tool, U5CRT Die With PUADP-1 Adap

Manufacturer Information

Brand	BURNDY
GTIN	00781810552759
Manufacturers Part Number	YA6CLBOX
UPC	781810552759

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 50

Weight Per each 0.0004

Uses, Certifications, and Standards

Application Wire Termination

standard UL 486A-486B