



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YAV25LTC14FX YAV25L-TC14FX *Burndy LLC*

Catalog Number	YAV25LTC14FX
Manufacturer	Burndy LLC
Description	1/0 Flex G, H, I, K, M, Dlo, 1/0 Awg (B/C) Cu, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Pink Color Code, 12 or 348 Die Index.
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	12
Material	Copper
pallet quantity	34800
Voltage Rating	35

Material, Color, and Finish

Color Code	PINK
------------	------

Descriptions

Description	YAV25L-TC14FX
extra long description	BUR YAV25LTC14FX 1/0FLEX 1/4STUD
Long Description	1/0 Flex G,H,I,K,M,DLO, 1/0 AWG (B/C) CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Pink Color Code, 12 or 348 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight, Die Index: 12, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Wire Strip Length: 11/16 IN, Color Code: Pink, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W25VT, W25RT, X25RT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W25VT, W25RT, X25RT Die, (2), Y35, Y39, Y750, PAT750 Tool, U25RT Die, (1), Y46 Tool, U25RT Die With PUADP-1 Adapter, (1).



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	BURNDY
GTIN	00781810022702
Manufacturers Part Number	YAV25LTC14FX
UPC	781810022702

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated

Packaging

Carton	1
Package	100
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B