



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YAV26LTC14FX YAV26L-TC14FX Burndy LLC

Catalog Number	YAV26LTC14FX
Manufacturer	Burndy LLC
Description	2/0 Flex G, H, I, K, M, Dlo, 2/0 Awg Cu, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, Ul/Csa, 90 C, Up to 35KV, Black Color Code, 13 Die Index.
Weight per unit	0.0700 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	13
Material	Copper
pallet quantity	29000
Voltage Rating	35

Material, Color, and Finish

Color Code	BLACK
------------	-------

Descriptions

Description	YAV26L-TC14FX
extra long description	BUR YAV26LTC14FX CUCOMP TERM 2/0 FL
Long Description	2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Black Color Code, 13 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Wire Strip Length: 13/16 IN, Tongue Angle: Straight, Die Index: 13, Temperature Rating: 90 DEG C, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W26VT, W26RT, X26RT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W26VT, W26RT, X26RT Die, (2), Y35, Y39, Y750, PAT750 Tool, U26RT Die, (1), Y46 Tool, U26RT Die With PUADP-1 Adapter, (1), Color Code: Black,

Manufacturer Information

Brand	BURNDY
GTIN	00781810022658
Manufacturers Part Number	YAV26LTC14FX
UPC	781810022658

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.07

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B