



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## Z132MV Low Profile Strip 1LMP 32W T8

*Lithonia Lighting - Acuity*

Catalog Number	Z132MV
Manufacturer	Lithonia Lighting - Acuity
Description	Lith Z132 MV Narrow Strip , 32W, In
Weight per unit	5.6 (lbs/each)
Product Category	Fluorescent Surface General Pu

### Features

Ballast Type	Electronic Ballast
dimensions	48" X 2-1/4" X 1-1/4"
Hardware	No
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	1
pallet quantity	224
Shape	Rectangular
Voltage Rating	120 to 277
Warranty	2
Wattage	32

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Height	2
Length	49
Width	3

### Descriptions

Description	LOW PROFILE STRIP 1LMP 32W T8
Long Description	LITH Z132 MV Narrow Strip , 32W, In
Product Type	Strip Light
Special Features	Ideal where high brightness and good illumination levels are required such as retail, light industrial and warehouses.

### Manufacturer Information

Brand	Lithonia Lighting
GTIN	00745976682736
Manufacturers Part Number	Z132MV
UPC	745976682736



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent Fixtures & Accessories  
Type ..... Strip Light

## Availability

Manufacturer Status ..... Inactive

## Packaging

Carton ..... 1  
Weight ..... 4  
Weight Per each ..... 5.5599

## Uses, Certifications, and Standards

Application ..... Automotive &  
Parking, Education, Government, Healthcare, Hospitality, House of  
Worship, Manufacturing, Offices & Banks, Power &  
Gas, Residential, Retail, Sports and  
Recreation, Transportation, Warehouses  
.....  
environmental conditions ..... Indoor  
Mounting ..... Surface, Suspended  
standard ..... CSA, UL