



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ZS124 Stem Mount Electronic Led Photocell 105-305V

Nsi Industries

| | |
|------------------|---|
| Catalog Number | ZS124 |
| Manufacturer | Nsi Industries |
| Description | The Tork ZS124 Stem Mount Instant Response Led Photocontrol Light Sensor Provides A Simple Way to Control Residential or Commercial Exterior Lights and Appliances Based On The Ambient Light Level. Features Include The Coated Circuit Board and Weather-Resistant Casing, Long-Life Zero-Cross Technology and The Time Delay That Prevents Stray Lights or Shadows From Triggering The Control. Designed For Applications Including Landscape Lighting, Perimeter and Security Lighting, Pole Lanterns or Signage. |
| Weight per unit | 0.2300 (lbs/each) |
| Product Category | Wiring Devices |

Features

| | |
|----------------|---------|
| Material | LEXAN |
| Voltage Rating | 105-305 |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|-------|-------|
| Color | White |
|-------|-------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | STEM MOUNT ELECTRONIC LED PHOTOCCELL 105-305V |
| extra long description | TORK ZS124 Zero Cross Stem Type On |
| Features | The TORK ZS124 provides professional-grade performance for a range of residential and commercial applications. This stem-mounted photocontrol light sensor with a plastic frame automatically detects nightfall, allowing you to run exterior lights from dusk to dawn. Use TORK photocontrols for your garage lights, landscape lighting, flood lamps or patio lights, or in commercial applications like lightposts or decorative lighting. The ZS124 saves you energy and money while adding security to your property at ni |
| Long Description | The TORK ZS124 stem mount instant response LED photocontrol light sensor provides a simple way to control residential or commercial exterior lights and appliances based on the ambient light level. Features include the coated circuit board and weather-resistant casing, long-life zero-cross technology and the time delay that prevents stray lights or shadows from triggering the control. Designed for applications including landscape lighting, perimeter and security lighting, pole lanterns or signage. |
| Product Type | Zero Cross Stem Type On 1.3-1.7 Off/On Ratio 1.5:1 105-305V |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00786261789136 |
| Manufacturers Part Number | ZS124 |
| UPC | 786261789136 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.23 |