



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ZL1NL485000LMFST 4' Led Strip 50K 5000LM

Lithonia Lighting - Acuity

Catalog Number	ZL1NL485000LMFST
Manufacturer	Lithonia Lighting - Acuity
Description	Z Series Led Strip Light, 48" Long, 5, 000 Nominal Lumens, Frosted, Diffuse, 120V-277V, 5000K, 80 CCT, White Finish, Sku - 253WJ9
Weight per unit	13.0 (lbs/each)
Product Category	Led Industrial Lighting

Features

average life	60
Fixture Type	Strip Light
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	5000
Material	Steel
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	5
Wattage	34

Material, Color, and Finish

Color	White
Finish	Gloss
Lens Color	WHITE
Lens Material	Acrylic

Dimensions and Weight

Height	2.5
Length	49
Width	3

Descriptions

Description	4' LED STRIP 50K 5000LM
extra long description	LITH ZL1N L48 5000LM FST MVOLT 50K
Long Description	Z SERIES LED STRIP LIGHT, 48" long, 5,000 nominal lumens, Frosted, diffuse, 120V-277V, 5000K, 80 CCT, White finish, SKU - 253WJ9
Product Type	Strip Light



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00190887789072
Manufacturers Part Number	ZL1N L48 5000LM FST MVOLT 50K
UPC	190887789072

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	Strip Light

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight Per each	13

Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Manufacturing, Offices & Banks, Residential, Retail, Warehouses
environmental conditions	Indoor
Mounting	Surface, Suspended
standard	CSADLC Premium, DLC Standard