



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **PW301W Pir Wall SWITCH Occ SNSR 120/277V W**

*Pass & Seymour/Legrand*

Catalog Number	PW301W
Manufacturer	Pass & Seymour/Legrand
Description	Wall Switch Occupancy Sensor, Sensor With Relay Type; 1.58 Inch W X 1.39 Inch D X 4.1 Inch H Size; White Finish; UL, Cul Approval; Small Office, Small Conference Room and Lunch/Break Room Application; 120/277 Vac At 50/60 HZ Voltage Rating; Wall Mounting
Weight per unit	0.4700 (lbs/each)
Product Category	Lighting Occupancy Sensors

### **Features**

Area Coverage	35 FT X 30 FT (MAJOR MOTION), 20 FT X 15 FT (MINOR MOTION)
Load Rating	0 to 1000 W at 120 VAC (Ballast/LED/Tungsten), 0 to 1200 W at 277 VAC (Ballast/LED), 1/6 HP at 120/277 VAC
Load Type	Ballast/Tungsten/LED
Sensor Type	PASSIVE INFRARED
Terminal Type	Screw
Time Delay	5/10/15/20/25/30 Min
Voltage Rating	120/277 VAC AT 50/60 HZ
Wall Plate Type	DECORATOR

### **Material, Color, and Finish**

Finish	white
--------	-------

### **Dimensions and Weight**

Size	1.58 Inch W x 1.39 Inch D x 4.1 Inch H
------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	Sensitivity Adjustment PIR (High/Low)
Commodity Description	LIGHTING OCCUPANCY SENSORS
Description	PIR WALL SWITCH OCC SNSR 120/277V W
extra long description	SENSOR WITH RELAY TYPE; 1.58 INCH W X 1.39 INCH D X 4.1 INCH H SIZE; WHITE FINISH; UL, CUL APPROVAL; SMALL OFFICE, SMALL CONFERENCE ROOM AND LUNCH/BREAK ROOM APPLICATION; 120/277 VAC AT 50/60 HZ VOLTAGE RATING; WALL MOUNTING; SCREW TERMINAL TYPE; 0 TO 1000 W AT 120 VAC (BALLAST/LED/TUNGSTEN), 0 TO 1200 W AT 277 VAC (BALLAST/LED), 1/6 HP AT 120/277 VAC LOAD RATING; DECORATOR WALL PLATE TYPE; PASSIVE INFRARED SENSOR TYPE; 35 FT X 30 FT (MAJOR MOTION), 20 FT X 15 FT (MINOR MOTION) AREA COVERAGE; BALLAST/TUNGS
Long Description	WALL SWITCH OCCUPANCY SENSOR, SENSOR WITH RELAY TYPE; 1.58 INCH W X 1.39 INCH D X 4.1 INCH H SIZE; WHITE FINISH; UL, CUL APPROVAL; SMALL OFFICE, SMALL CONFERENCE ROOM AND LUNCH/BREAK ROOM APPLICATION; 120/277 VAC AT 50/60 HZ VOLTAGE RATING; WALL MOUNTING
Product Type	Wall Switch Occupancy Sensor

## Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00754182935260
Manufacturers Part Number	PW-301-W
UPC	754182935260

## Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	SENSOR WITH RELAY

## Packaging

Carton	1
Package	40
Weight Per each	0.47

## Uses, Certifications, and Standards

Application	Small Office, Small Conference Room and Lunch/Break Room
Approval	UL, CUL
Mounting	WALL