

Eaton 11100R6513

Catalog Number: 11100R6513

Eaton Comet 18mm tubular photoelectric sensor, Through Beam, Wide right, Power, 6.6 ft, PVC, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)

General specifications



Product Name	Catalog Number
Eaton Comet 18mm tubular photoelectric sensor	11100R6513
	UPC 782113819204
Product Length/Depth	Product Height
2.55 in	0.71 in
Product Width	Product Weight
0.47 in	0.7 lb
Warranty	Certifications
3 year	UL Recognized cUL Recognized

defaultTaxonomyAttributeLabel

Type

Photoelectric Sensor

Cable type

Polyvinyl Chloride (PVC)

Enclosure material

Polyurethane foam (RIM)

Series

Comet

Sensor type

Through beam

Input voltage

20-264 Vac at 50/60 Hz, 15-30 Vdc (NPN)

LED indicator

Power

Cord length

79.2 ft

Operating temperature - max

158 °F

Operating temperature - min

-4 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 4, NEMA 4X, NEMA 6, NEMA 12,
NEMA 13, IP69K

Resources

Brochures

[Comet series - Photoelectric sensors](#)

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - 11100R6513](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)