

Eaton 11102AF1213

Catalog Number: 11102AF1213

Eaton Comet 18mm tubular photoelectric sensor, Photoelectric, 0.71 diameter, Forward Viewing, Sensor distance: 80 Ft., Lens: Polycarbonate Cable, Jacket: PVC Body, 12 Ft. (3.7m) Cable, 20-264 Vac/15-30 Vdc input

General specifications



Product Name	Catalog Number
Eaton Comet 18mm tubular photoelectric sensor	11102AF1213
	UPC
	782114023655
Product Length/Depth	Product Height
0.47 in	2.75 in
Product Width	Product Weight
0.71 in	0.2875 lb
Warranty	Compliances
3 year	Contact Manufacturer

defaultTaxonomyAttributeLabel

Cable type

Polyvinyl Chloride (PVC)

Enclosure material

Cable jacket: PVC

Lens: polycarbonate

Body: structural polyurethane foam

Operating mode

Thru-beam

Connection

12 ft (3.7 m) cable

Sensor type

Through beam

Switch type

Photoelectric

Input voltage

20-264 Vac, 15-30 Vdc

LED indicator

Power on: red

Cord length

144 ft

Operating temperature - max

158 °F

Operating temperature - min

-4 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13, IP68, IP69K

Resources

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

Specifications and datasheets

[Eaton Specification Sheet - 11102AF1213](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)