



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



12100A6513 Comet, Thru-Beam Detector Wideangle, 20-264 Vac/DC W Eaton Corp

| | |
|------------------|--|
| Catalog Number | 12100A6513 |
| Manufacturer | Eaton Corp |
| Description | Eaton Comet 18MM Tubular Photoelectric Sensor, Through Beam, 20 FT Range, Forward Viewing, Output On, 6.6 FT, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, PVC, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN) |
| Weight per unit | 0.6700 (lbs/each) |
| Product Category | Sensor Accessories |

Features

dimensions 2.2000 IN X 0.4700 IN X 0.7100 IN

Descriptions

| | |
|------------------------|---|
| Description | COMET,THRU-BEAM DETECTOR WIDEANGLE,20-264 VAC/DC W |
| extra long description | ETN 12100A6513 PHOTO SENSOR,TB DET, |
| Features | Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem. |
| Long Description | Eaton Comet 18mm tubular photoelectric sensor,Through Beam, 20 ft range, Forward Viewing, Output ON, 6.6 ft, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, PVC, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN) |
| Product Type | Photo Sensor, TB Det, Wide Angle, Acdc, CBL |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN | 00782113821931 |
| Manufacturers Part Number | 12100A6513 |
| UPC | 782113821931 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------|
| Category Description | PROXIMITY SWITCHES AND CORDSETS |
| Type | Tubular photoelectric sensor |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.67 |

Uses, Certifications, and Standards

| | |
|--------------------------------|---|
| Application | Vehicles: On-Road - PickUp & Delivery: Food |
| Operating Temperature standard | -4° to 158°F (-20° to 70°C) cUL Recognized,UL Recognized |