



1212HSE Wway 12X12 N1 End PLT, 3"Ko

Cooper B-Line/Cable Tray

Catalog Number	1212HSE
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wireway End, 1.50 Inch Knockout, Wireway End, Nema 1, Steel, Ansi 61 Gray Painted, 12" X 12"
Weight per unit	3.1 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

Cover Type	HINGED
dimensions	12.0000 IN X 11.9000 IN X 12.0000 IN
Material	Steel

Material, Color, and Finish

Finish	Gray
--------	------

Dimensions and Weight

Height	12.00 In
Width	12.00 In

Descriptions

Description	WWAY 12X12 N1 END PLT,3"KO
extra long description	B-LINE 1212 HSE HINGE SCREW CVR WIR
Features	Eaton's B-Line series wiring troughs provide reliable environmental protection and are used to house runs of control and power cable in wiring, junction, pull, and termination applications.
Long Description	Eaton B-Line series wireway end, 1.50 inch Knockout, Wireway end, NEMA 1, Steel, ANSI 61 gray painted, 12" X 12"
Product Type	Hinge Screw CVR Wireway, End 12X12

Manufacturer Information

Brand	Eaton
GTIN	00782051479560
Manufacturers Part Number	1212 HSE
UPC	782051479560

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Wireway end

Packaging

Carton	1
Weight Per each	3.103



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7929 N Sam Houston Pkwy W Suite 100
77064-0000, TX Houston
Phone: 281-345-1143
Fax: 281-345-7697

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherInd Facilities & Factories - Facility: Lighting and Lighting ControlsInd Facilities & Factories - Facility: Critical PowerCommercial / Institutional Buildings / Structures - Critical PowerInd Facilities & Factories - Facility: Safety and Security SystemsCommercial / Institutional Buildings / Structures - Power Distribution and ControlsInd Facilities & Factories - Industrial Facilities/Factories - Ot

Enclosure standard

NEMA 1, IP30

UL Listed, CSA C22.2, NEMA