



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6312A Airport Freeway  
76117-0000, TX Ft. Worth  
Phone: 682-647-1594  
Fax: 682-647-1528



## 13101AQD07 4" PPRX Conn Version DC Eaton Corp

Catalog Number	13101AQD07
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Perfect Prox Photoelectric Sensor, Back Ground Suppression, 4 In Range, Forward Viewing, Output On, M12, 100 Ma PNP, 250 Ma NPN At 10-30 VDC, 4 Pin, NPN and PNP Open Collector, 10-30 VDC
Weight per unit	0.6700 (lbs/each)
Product Category	Photoelectric Sensors

### Features

connection	Connector M12
------------	---------------

### Dimensions and Weight

Height	0.71
Length	2.06
Width	0.47

### Descriptions

Description	4" PPRX CONN VERSION DC
extra long description	ETN 13101AQD07 4" PPRX CONN VERSION
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Perfect Prox Photoelectric Sensor, Back Ground Suppression, 4 in range, Forward Viewing, Output ON, M12, 100 mA PNP, 250 mA NPN at 10-30 Vdc, 4 pin, NPN and PNP open collector, 10-30 Vdc
Product Type	4" PPRX Conn Version DC

### Manufacturer Information

Brand	Eaton
GTIN	00782113938318
Manufacturers Part Number	13101AQD07
UPC	782113938318

### Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

### Packaging

Carton	1
Weight Per each	0.67



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6312A Airport Freeway  
76117-0000, TX Ft. Worth  
Phone: 682-647-1594  
Fax: 682-647-1528

## Uses, Certifications, and Standards

Application .....	Vehicles: On-Road - PickUp & Delivery: Food .....
Operating Temperature .....	-40° to 158°F (-40° to 70°C) .....
standard .....	UL Recognized,cUL Recognized .....