



SAFETY DATA SHEET

1. Identification

Product identifier	Fire Ant Killer
Other means of identification	
Product code	14037
Registration number	EPA: 55809-3
Recommended use	Fire ant killer spray
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency (CHEMTREC)	800-424-9300 (US) 703-527-3887 (International)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Flammable aerosols Gases under pressure	Category 1 Compressed gas
Health hazards	Skin corrosion/irritation Specific target organ toxicity, single exposure Aspiration hazard	Category 2 Category 3 narcotic effects Category 1
Environmental hazards	Hazardous to the aquatic environment, acute hazard Hazardous to the aquatic environment, long-term hazard	Category 1 Category 1
OSHA defined hazards	Not classified.	

Label elements



Signal word	Danger
Hazard statement	Extremely flammable aerosol. Contains gas under pressure; may explode if heated. May be fatal if swallowed and enters airways. Causes skin irritation. May cause drowsiness or dizziness. Very toxic to aquatic life. Very toxic to aquatic life with long lasting effects.
Precautionary statement	
Prevention	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Do not apply while equipment is energized. Pressurized container: Do not pierce or burn, even after use. Extinguish all flames, pilot lights and heaters. Vapors will accumulate readily and may ignite. Use only with adequate ventilation; maintain ventilation during use and until all vapors are gone. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist or vapor. Wash thoroughly after handling. Wear protective gloves. Avoid release to the environment.

Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation occurs: Get medical attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. Collect spillage.
Storage	Store in a well-ventilated place. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Exposure to high temperature may cause can to burst.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Distillates (petroleum), hydrotreated light		64742-47-8	90 - 100
Carbon dioxide		124-38-9	1 - 3
Tetramethrin		7696-12-0	0.2
d-Phenothrin		26002-80-2	0.1

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing. Rinse skin with water/shower. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Continue rinsing. Remove contact lenses, if present and easy to do. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs. Never give anything by mouth to a victim who is unconscious or is having convulsions.
Most important symptoms/effects, acute and delayed	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Aspiration may cause pulmonary edema and pneumonitis. Skin irritation. May cause redness and pain.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Alcohol resistant foam. Water fog. Dry chemical powder. Dry chemicals. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Contents under pressure. Pressurized container may rupture when exposed to heat or flame. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Containers should be cooled with water to prevent vapor pressure build up.
General fire hazards	Extremely flammable aerosol. Contents under pressure. Pressurized container may rupture when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist or vapor. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS. Prevent entry into waterways, sewer, basements or confined areas.

Environmental precautions

Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground. Inform appropriate managerial or supervisory personnel of all environmental releases.

7. Handling and storage

Precautions for safe handling

Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid breathing mist or vapor. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, please see the product label.

Conditions for safe storage, including any incompatibilities

Level 3 Aerosol.

Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Carbon dioxide (CAS 124-38-9)	PEL	9000 mg/m3
		5000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
Carbon dioxide (CAS 124-38-9)	STEL	30000 ppm
	TWA	5000 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Carbon dioxide (CAS 124-38-9)	STEL	54000 mg/m3
		30000 ppm
	TWA	9000 mg/m3
Distillates (petroleum), hydrotreated light (CAS 64742-47-8)		5000 ppm
	TWA	100 mg/m3

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Wear protective gloves such as: Neoprene. Nitrile.
Other	Wear appropriate chemical resistant clothing.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Aerosol.
Color	Clear.
Odor	Petroleum.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	-72.4 °F (-58 °C) estimated
Initial boiling point and boiling range	336 °F (168.9 °C) estimated
Flash point	205 °F (96.1 °C) Pensky-Martens Closed Cup
Evaporation rate	Slow.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	0.5 % estimated
Flammability limit - upper (%)	5.5 % estimated
Vapor pressure	1637.3 hPa estimated
Vapor density	> 2 (air = 1)
Relative density	0.82 estimated
Solubility (water)	Negligible.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	410 °F (210 °C) estimated
Decomposition temperature	Not available.
Viscosity (kinematic)	Not available.
Percent volatile	95.8 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.

Conditions to avoid	Heat, flames and sparks. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents. Strong acids. Strong bases.
Hazardous decomposition products	Carbon oxides.

11. Toxicological information

Information on likely routes of exposure

Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.
Inhalation	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Prolonged inhalation may be harmful.
Skin contact	Causes skin irritation.
Eye contact	Direct contact with eyes may cause temporary irritation.

Symptoms related to the physical, chemical and toxicological characteristics
May cause drowsiness and dizziness. Headache. Nausea, vomiting. Aspiration may cause pulmonary edema and pneumonitis. Skin irritation. May cause redness and pain.

Information on toxicological effects

Acute toxicity May be fatal if swallowed and enters airways. Narcotic effects.

Product	Species	Test Results
Fire Ant Killer		
Acute		
<i>Dermal</i>		
LD50	Rabbit	2093.4304 mg/kg estimated
<i>Inhalation</i>		
LC50	Rat	5.356 mg/l, 4 Hours estimated
<i>Oral</i>		
LD50	Rat	5138.2534 mg/kg estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Causes skin irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory sensitization	Not available.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	May cause drowsiness and dizziness.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	May be fatal if swallowed and enters airways. If aspirated into lungs during swallowing or vomiting, may cause chemical pneumonia, pulmonary injury or death.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity Very toxic to aquatic life. Very toxic to aquatic life with long lasting effects.

Product	Species	Test Results
Fire Ant Killer		
Aquatic		
<i>Acute</i>		
Crustacea	EC50 Daphnia	54.8358 mg/l, 48 hours estimated

Product		Species	Test Results
Fish	LC50	Fish	1.5721 mg/l, 96 hours estimated
Components		Species	Test Results
Distillates (petroleum), hydrotreated light (CAS 64742-47-8)			
Aquatic			
<i>Acute</i>			
Fish	LC50	Bluegill (<i>Lepomis macrochirus</i>)	2.2 mg/l, 96 hours
Tetramethrin (CAS 7696-12-0)			
Aquatic			
<i>Acute</i>			
Crustacea	EC50	Water flea (<i>Daphnia magna</i>)	0.11 mg/l, 48 hours
Fish	LC50	Rainbow trout,donaldson trout (<i>Oncorhynchus mykiss</i>)	0.0037 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential No data available.

Partition coefficient n-octanol / water (log Kow)

Tetramethrin 4.58

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal of waste from residues / unused products This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). If empty: Place in trash or offer for recycling this container. If partly filled: Call your local solid waste agency for disposal instructions. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

Hazardous waste code Not regulated.

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN number UN1950
UN proper shipping name Aerosols, flammable, Limited Quantity
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Label(s) 2.1
Packing group Not applicable.
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.
Special provisions N82
Packaging exceptions 306
Packaging non bulk None
Packaging bulk None

IATA

UN number UN1950
UN proper shipping name Aerosols, flammable, Limited Quantity
Transport hazard class(es)
Class 2.1
Subsidiary risk -
Packing group Not applicable.
Environmental hazards No.
ERG Code 10L
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

Other information

Passenger and cargo aircraft Allowed.
Cargo aircraft only Allowed.

IMDG

UN number UN1950
UN proper shipping name AEROSOLS, LIMITED QUANTITY, MARINE POLLUTANT
Transport hazard class(es)
Class 2
Subsidiary risk -
Packing group Not applicable.
Environmental hazards
Marine pollutant Yes
EmS Not available.
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

d-Phenothrin (CAS 26002-80-2)
Tetramethrin (CAS 7696-12-0)

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

US EPA Federal Insecticide, Fungicide, and Rodenticide Act (FIFRA)

FIFRA Information This chemical is a pesticide product registered by the United States Environmental Protection Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets (SDS), and for workplace labels of non-pesticide chemicals. The hazard information required on the pesticide label is reproduced below. The pesticide label also includes other important information, including directions for use.

Signal word Warning.

Hazard statement Harmful if absorbed through skin. Causes moderate eye irritation.
This product is registered for sale in the following states: AL, AR, AZ, CA, FL, GA, KY, LA, MS, NC, NM, OK, SC, TN, TX, and VA. Sale in any other state or outside of the United States is prohibited.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Section 311/312 Immediate Hazard - Yes
Hazard categories Delayed Hazard - No
 Fire Hazard - Yes
 Pressure Hazard - Yes
 Reactivity Hazard - No

SARA 302 Extremely hazardous substance No

US state regulations**US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)**

Not listed.

US. New Jersey Worker and Community Right-to-Know Act

Carbon dioxide (CAS 124-38-9)
 Distillates (petroleum), hydrotreated light (CAS 64742-47-8)
 d-Phenothrin (CAS 26002-80-2)
 Tetramethrin (CAS 7696-12-0)

US. Massachusetts RTK - Substance List

Carbon dioxide (CAS 124-38-9)

US. Pennsylvania Worker and Community Right-to-Know Law

Carbon dioxide (CAS 124-38-9)
 Distillates (petroleum), hydrotreated light (CAS 64742-47-8)

US. Rhode Island RTK

d-Phenothrin (CAS 26002-80-2)
 Tetramethrin (CAS 7696-12-0)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

Volatile organic compounds (VOC) regulations**EPA**

VOC content (40 CFR 51.100(s)) 96.5 %

Consumer products (40 CFR 59, Subpt. C) Compliant

State

Consumer products This product is regulated as a Crawling Bug Insecticide. This product is compliant for use in all 50 states.

VOC content (CA) 1.4 %

VOC content (OTC) 1.4 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 03-12-2015
Prepared by Allison Cho
Version # 01
Further information CRC # 431J
HMIS® ratings Health: 2
Flammability: 3
Physical hazard: 0
Personal protection: B

NFPA ratings Health: 2
Flammability: 3
Instability: 0

NFPA ratings



Disclaimer

CRC cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries.