



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1350E8547 5' Diffuse Reflective, DC, NPN/PNP, Body Micro, W/Timi Eaton Corp

Catalog Number	1350E8547
Manufacturer	Eaton Corp
Description	Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Sensor Dist. 5 FT., 250 Ma Max DC, NPN/PNP Open Collector, 250 Ma At 40 VDC, 4 Pin M12 Connector, 10-40 VDC Input, Reverse Polarity, Short Circuit and Overload, Yes
Weight per unit	0.4000 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	4-pin M12 connector
dimensions	1.9100 IN X 1.8100 IN X 4.0100 IN

Descriptions

Description	5' DIFFUSE REFLECTIVE,DC,NPN/PNP,BODY MICRO,W/TIMI
extra long description	ETN 1350E-8547 PHOTO SENSOR,DIFFUSE
Features	Enhanced 50 series high-performance sensors offer flexibility, durability and high optical performance with a fully potted construction that makes these sensors ideal for use in areas subject to washdown, high shock and high vibration. Three output types, four time-delay functions, six sensing modes and four connection styles allow you to tailor the sensor to meet your exact needs
Long Description	Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Sensor dist. 5 Ft., 250 mA max DC, NPN/PNP Open Collector, 250 mA at 40 Vdc, 4 Pin M12 Connector, 10-40 Vdc input, Reverse polarity, short circuit and overload, Yes
Product Type	Photo Sensor, Diffuse, DC, NPN/PNP, Micro, TD

Manufacturer Information

Brand	Eaton
GTIN	00782116111503
Manufacturers Part Number	1350E-8547
UPC	782116111503

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Photoelectric Sensor

Packaging

Carton	1
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
Operating Temperature	-13° to 131°F (-25° to 55°C)
standard	CSA Certified, Contact Manufacturer, CE Marked