



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1550B6511 Self-Contained, 115VAC, Cable W/Fiber Optic Adaptor

Eaton Corp

Catalog Number	1550B6511
Manufacturer	Eaton Corp
Description	Eaton 50 Series Photoelectric Sensor, Right Angle, Sensor Distance: Depends On The Fiberoptic Cables Used, Body: Noryl, Lens: Nylon Encl, Depends On Output Device Max Ac/DC, 6.6 FT. (2M) Cable, 90-132 Vac Input, Fiberoptic, Infrared
Weight per unit	0.6100 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	6.6 ft (2 m) cable
------------	--------------------

Dimensions and Weight

Height	3.19
Length	1.64
Width	1.83

Descriptions

Description	SELF-CONTAINED,115VAC,CABLE W/FIBER OPTIC ADAPTOR
extra long description	ETN 1550B-6511 PHOTO SENSOR,FIBEROP
Features	50 series photoelectric sensors offer flexibility, durability and high optical performance in a cost effective self-contained package. Choose from four output device modules, four logic function modules, five sensing modes and two types of connection to tailor the sensor to exactly meet your needs. A removable sealed cover allows access to the interchangeable modules.
Long Description	Eaton 50 Series Photoelectric Sensor, Right Angle, Sensor distance: Depends on the fiberoptic cables used, Body: Noryl, Lens: Nylon encl, Depends on Output Device max AC/DC, 6.6 Ft. (2m) Cable, 90-132 Vac input, Fiberoptic, Infrared
Product Type	Photo Sensor, Fiberoptic, 115VAC, CBL

Manufacturer Information

Brand	Eaton
GTIN	00782113825625
Manufacturers Part Number	1550B-6511
UPC	782113825625

Taxonomies, Classifications, and Categories

Type	Photoelectric Sensor
------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.61

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
Operating Temperature standard	-40° to 158°F (-40° to 70°C) UL Listed, CSA Certified, Contact Manufacturer