



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1610C Connector Nema 5-15 15A 125V Small Yellow

Ericson MFG

Catalog Number	1610C
Manufacturer	Ericson MFG
Description	Connector Nema 5-15, Perma-Link Industrial Grade Yellow Wiring Device, Straight 15 Amp 125V 1PH 2P/3W, Size = SM, 1547
Weight per unit	0.2200 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	15
amps	15
Device Type	Connector
Material	Non-Slip Elastomeric Housing, Solid Brass Blade
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125

Descriptions

Description	CONNECTOR NEMA 5-15 15A 125V SMALL YELLOW
extra long description	ERIC 1610-C WD PERMA-LINK CONN NEMA
Long Description	CONNECTOR NEMA 5-15, PERMA-LINK INDUSTRIAL GRADE YELLOW WIRING DEVICE, STRAIGHT 15 AMP 125V 1PH 2P/3W, SIZE = SM, 1547
Product Type	WD Perma-Link Conn Nema 5-15 Yel
Special Features	Features: Perma-Link Plugs And Connectors All Engineered With :- Dead-Front, Back-Wired Design; Solid Brass Blades; Transparent Back-Plate For Easy Inspection Of Individual Wiring Chamber; Captive Assembly And Terminal Screws Reduce The Risk Of Losing Small Parts; No-Slip Elastomeric Housing With Finger-Grips; High Visibility Ericson Dual-Color Safety System; Nema Configurations And A Variety Of Specialty Non-Nema Devices; 15 AMP, 20 AMP, 30 AMP And 50 AMP Models; Standard Voltages From 120 V Through 600 V

Manufacturer Information

Brand	ERICSON
GTIN	00782862587508
Manufacturers Part Number	1610-C
UPC	782862587508

Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	Wiring Devices



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.22

Uses, Certifications, and Standards

Application	For Industrial/Construction Environments
nema rating	5-15
standard	UL Listed, Meets IEC, OSHA