



# SAFETY DATA SHEET

## 1. Identification

**Product identifier** QD® Contact Cleaner - 11 oz

**Other means of identification**

**Product Code** No. 02130 (Item# 1003218)

**Recommended use** Electronic cleaner

**Recommended restrictions** None known.

**Manufacturer/Importer/Supplier/Distributor information**

**Manufactured or sold by:**

**Company name** CRC Industries, Inc.

**Address** 885 Louis Dr.  
Warminster, PA 18974 US

**Telephone**

**General Information** 215-674-4300

**Technical Assistance** 800-521-3168

**Customer Service** 800-272-4620

**24-Hour Emergency (CHEMTREC)** 800-424-9300 (US)

**Website** www.crcindustries.com

## 2. Hazard(s) identification

<b>Physical hazards</b>	Flammable aerosols	Category 1
	Gases under pressure	Liquefied gas
<b>Health hazards</b>	Skin corrosion/irritation	Category 2
	Specific target organ toxicity, single exposure	Category 3 narcotic effects
	Aspiration hazard	Category 1
<b>Environmental hazards</b>	Hazardous to the aquatic environment, acute hazard	Category 2
	Hazardous to the aquatic environment, long-term hazard	Category 2
<b>OSHA defined hazards</b>	Not classified.	

**Label elements**



**Signal word** Danger

**Hazard statement** Extremely flammable aerosol. Contains gas under pressure; may explode if heated. May be fatal if swallowed and enters airways. Causes skin irritation. May cause drowsiness or dizziness.

**Precautionary statement**

**Prevention** Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Do not apply while equipment is energized. Extinguish all flames, pilot lights, and heaters. Vapors will accumulate readily and may ignite. Use only outdoors or in a well-ventilated area. Maintain ventilation during use and until all vapors are gone. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist/vapor. Wash thoroughly after handling. Wear protective gloves.

<b>Response</b>	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell.
<b>Storage</b>	Store in a well-ventilated place. Keep container tightly closed. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Exposure to high temperature may cause can to burst.
<b>Disposal</b>	Dispose of contents/container in accordance with local/regional/national regulations.
<b>Hazard(s) not otherwise classified (HNOC)</b>	None known.
<b>Supplemental information</b>	None.

### 3. Composition/information on ingredients

#### Mixtures

Chemical name	Common name and synonyms	CAS number	%
naphtha (petroleum), hydrotreated light		64742-49-0	60 - 70
1,1-difluoroethane	HFC-152a	75-37-6	20 - 30
naphtha (petroleum), light alkylate		64741-66-8	5 - 10
isopropyl alcohol		67-63-0	1 - 5

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

### 4. First-aid measures

<b>Inhalation</b>	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a poison center or doctor/physician if you feel unwell.
<b>Skin contact</b>	Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
<b>Eye contact</b>	Rinse with water. Get medical attention if irritation develops and persists.
<b>Ingestion</b>	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
<b>Most important symptoms/effects, acute and delayed</b>	Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Skin irritation. May cause redness and pain.
<b>Indication of immediate medical attention and special treatment needed</b>	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
<b>General information</b>	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

### 5. Fire-fighting measures

<b>Suitable extinguishing media</b>	Dry chemical powder.
<b>Unsuitable extinguishing media</b>	Do not use water jet as an extinguisher, as this will spread the fire.
<b>Specific hazards arising from the chemical</b>	Contents under pressure. Pressurized container may rupture when exposed to heat or flame. During fire, gases hazardous to health may be formed.
<b>Special protective equipment and precautions for firefighters</b>	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
<b>Fire-fighting equipment/instructions</b>	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. Use standard firefighting procedures and consider the hazards of other involved materials. In the event of fire and/or explosion do not breathe fumes.
<b>General fire hazards</b>	Extremely flammable aerosol. Contents under pressure. Pressurized container may rupture when exposed to heat or flame.

---

## 6. Accidental release measures

### Personal precautions, protective equipment and emergency procedures

Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist/vapor. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

### Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. Prevent product from entering drains. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.

### Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

---

## 7. Handling and storage

### Precautions for safe handling

Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid breathing mist/vapors. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

### Conditions for safe storage, including any incompatibilities

Level 3 Aerosol.

Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50 °C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store in tightly closed container. Store in a well-ventilated place. Stored containers should be periodically checked for general condition and leakage. Store away from incompatible materials (see Section 10 of the SDS).

---

## 8. Exposure controls/personal protection

### Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

#### US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
isopropyl alcohol (CAS 67-63-0)	PEL	980 mg/m3
		400 ppm
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)	PEL	400 mg/m3
		100 ppm

#### US. ACGIH Threshold Limit Values

Components	Type	Value
isopropyl alcohol (CAS 67-63-0)	STEL	400 ppm
	TWA	200 ppm

#### US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
isopropyl alcohol (CAS 67-63-0)	STEL	1225 mg/m3

**US. NIOSH: Pocket Guide to Chemical Hazards**

Components	Type	Value
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)		500 ppm
	TWA	980 mg/m3
		400 ppm
	TWA	400 mg/m3
		100 ppm

**US. Workplace Environmental Exposure Level (WEEL) Guides**

Components	Type	Value
1,1-difluoroethane (CAS 75-37-6)	TWA	2700 mg/m3
		1000 ppm

**Biological limit values****ACGIH Biological Exposure Indices**

Components	Value	Determinant	Specimen	Sampling Time
isopropyl alcohol (CAS 67-63-0)	40 mg/l	Acetone	Urine	*

\* - For sampling details, please see the source document.

**Appropriate engineering controls**

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station and safety shower.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin protection****Hand protection**

Wear protective gloves such as: Polyvinyl alcohol (PVA). Viton/butyl.

**Other**

Wear appropriate chemical resistant clothing.

**Respiratory protection**

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

**Thermal hazards**

Wear appropriate thermal protective clothing, when necessary.

**General hygiene considerations**

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

**9. Physical and chemical properties****Appearance****Physical state**

Liquid.

**Form**

Aerosol.

**Color**

Colorless.

**Odor**

Hydrocarbon-like.

**Odor threshold**

Not available.

**pH**

Not available.

**Melting point/freezing point**

Not available.

**Initial boiling point and boiling range**

201.2 °F (94 °C) estimated

**Flash point**

15.8 °F (-9.0 °C) estimated

**Evaporation rate**

Very fast.

**Flammability (solid, gas)**

Not available.

## Upper/lower flammability or explosive limits

<b>Flammability limit - lower (%)</b>	0.9 % estimated
<b>Flammability limit - upper (%)</b>	13 % estimated
<b>Vapor pressure</b>	1117.5 hPa estimated
<b>Vapor density</b>	> 1 (air = 1)
<b>Relative density</b>	0.75 estimated
<b>Solubility(ies)</b>	
<b>Solubility (water)</b>	Negligible.
<b>Partition coefficient (n-octanol/water)</b>	Not available.
<b>Auto-ignition temperature</b>	509 °F (265 °C) estimated
<b>Decomposition temperature</b>	Not available.
<b>Viscosity</b>	Not available.
<b>Percent volatile</b>	82.1 % estimated

---

## 10. Stability and reactivity

<b>Reactivity</b>	The product is stable and non-reactive under normal conditions of use, storage and transport.
<b>Chemical stability</b>	Material is stable under normal conditions.
<b>Possibility of hazardous reactions</b>	No dangerous reaction known under conditions of normal use.
<b>Conditions to avoid</b>	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. Contact with incompatible materials.
<b>Incompatible materials</b>	Strong oxidizing agents.
<b>Hazardous decomposition products</b>	Carbon oxides. Sulfur oxides.

---

## 11. Toxicological information

### Information on likely routes of exposure

<b>Inhalation</b>	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Prolonged inhalation may be harmful.
<b>Skin contact</b>	Causes skin irritation.
<b>Eye contact</b>	Based on available data, the classification criteria are not met.
<b>Ingestion</b>	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

### Symptoms related to the physical, chemical and toxicological characteristics

Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Skin irritation. May cause redness and pain.

### Information on toxicological effects

**Acute toxicity** May be fatal if swallowed and enters airways.

<b>Components</b>	<b>Species</b>	<b>Test Results</b>
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)		
<b>Acute</b>		
<b>Dermal</b>		
LD50	Rat	> 2000 mg/kg
<b>Inhalation</b>		
<i>Vapor</i>		
LC50	Rat	> 5.2 mg/l, 4 hours
<b>Oral</b>		
LD50	Rat	> 5000 mg/kg

**Skin corrosion/irritation** Causes skin irritation.

**Serious eye damage/eye irritation** Based on available data, the classification criteria are not met.

## Respiratory or skin sensitization

**Respiratory sensitization** Not a respiratory sensitizer.

**Skin sensitization** This product is not expected to cause skin sensitization.

**Germ cell mutagenicity** No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

**Carcinogenicity** Not classifiable as to carcinogenicity to humans.

### IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

### OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

### US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

**Reproductive toxicity** This product is not expected to cause reproductive or developmental effects.

**Specific target organ toxicity - single exposure** May cause drowsiness and dizziness.

**Specific target organ toxicity - repeated exposure** Not classified.

**Aspiration hazard** May be fatal if swallowed and enters airways.

**Chronic effects** Prolonged inhalation may be harmful.

---

## 12. Ecological information

**Ecotoxicity** Toxic to aquatic life with long lasting effects.

**Persistence and degradability** No data is available on the degradability of any ingredients in the mixture.

### Bioaccumulative potential

#### Partition coefficient n-octanol / water (log Kow)

1,1-difluoroethane 0.75

isopropyl alcohol 0.05

#### Bioconcentration factor (BCF)

naphtha (petroleum), hydrotreated light 10 - 2500

**Mobility in soil** No data available.

**Other adverse effects** No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

---

## 13. Disposal considerations

**Disposal instructions** If discarded, this product is considered a RCRA ignitable waste, D001. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

**Hazardous waste code** D001: Waste Flammable material with a flash point <140 F

**Contaminated packaging** Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

---

## 14. Transport information

### DOT

**UN number** UN1950

**UN proper shipping name** Aerosols, flammable, Limited Quantity

**Transport hazard class(es)**

**Class** 2.1

**Subsidiary risk** -

**Label(s)** 2.1

**Packing group** -

**Environmental hazards**

**Marine pollutant** Yes, but exempt from the regulations.

**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.

**Special provisions** N82

**Packaging exceptions** 306

**Packaging non bulk** None  
**Packaging bulk** None


**IATA**

**UN number** UN1950  
**UN proper shipping name** Aerosols, flammable, Limited Quantity  
**Transport hazard class(es)**  
**Class** 2.1  
**Subsidiary risk** -  
**Packing group** -  
**ERG Code** 10L  
**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.  
**Other information**  
**Passenger and cargo aircraft** Allowed with restrictions.  
**Cargo aircraft only** Allowed with restrictions.


**IMDG**

**UN number** UN1950  
**UN proper shipping name** AEROSOLS, Limited Quantity  
**Transport hazard class(es)**  
**Class** 2.1  
**Subsidiary risk** -  
**Packing group** -  
**Environmental hazards**  
**Marine pollutant** Yes, but exempt from the regulations.  
**EmS** F-D, S-U  
**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.

**DOT; IMDG**



**IATA**



---

## 15. Regulatory information

**US federal regulations** This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

**TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)**  
Not regulated.

**SARA 304 Emergency release notification**  
Not regulated.

**OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)**  
Not listed.

**CERCLA Hazardous Substance List (40 CFR 302.4)**

Not listed.

**CERCLA Hazardous Substances: Reportable quantity**

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

**Other federal regulations****Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

**Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)**

1,1-difluoroethane (CAS 75-37-6)

**Safe Drinking Water Act (SDWA)** Contains component(s) regulated under the Safe Drinking Water Act.

**FEMA Priority Substances Respiratory Health and Safety in the Flavor Manufacturing Workplace**

isopropyl alcohol (CAS 67-63-0)

Low priority

**Food and Drug Administration (FDA)** Not regulated.

**Superfund Amendments and Reauthorization Act of 1986 (SARA)**

**Classified hazard categories** Flammable (gases, aerosols, liquids, or solids)  
Gas under pressure  
Skin corrosion or irritation  
Specific target organ toxicity (single or repeated exposure)  
Aspiration hazard

**SARA 302 Extremely hazardous substance**

Not listed.

**SARA 311/312 Hazardous chemical** Yes

**SARA 313 (TRI reporting)**  
Not regulated.

**US state regulations****US. New Jersey Worker and Community Right-to-Know Act**

1,1-difluoroethane (CAS 75-37-6)  
isopropyl alcohol (CAS 67-63-0)  
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)

**US. Massachusetts RTK - Substance List**

1,1-difluoroethane (CAS 75-37-6)  
isopropyl alcohol (CAS 67-63-0)  
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)

**US. Pennsylvania Worker and Community Right-to-Know Law**

isopropyl alcohol (CAS 67-63-0)  
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)

**US. Rhode Island RTK**

isopropyl alcohol (CAS 67-63-0)  
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)

**California Proposition 65**

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))**

isopropyl alcohol (CAS 67-63-0)  
naphtha (petroleum), hydrotreated light (CAS 64742-49-0)  
naphtha (petroleum), light alkylate (CAS 64741-66-8)

**Volatile organic compounds (VOC) regulations****EPA**

**VOC content (40 CFR 51.100(s))** 74.9 %



**Consumer products  
(40 CFR 59, Subpt. C)** Not regulated

**State**

**Consumer products** This product is regulated as an Electronic Cleaner. This product is compliant for use in all 50 states.

**VOC content (CA)** 74.9 %

**VOC content (OTC)** 74.9 %

**International Inventories**

<b>Country(s) or region</b>	<b>Inventory name</b>	<b>On inventory (yes/no)*</b>
Australia	Australian Inventory of Industrial Chemicals (AICIS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

\*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

---

**16. Other information, including date of preparation or last revision**

**Issue date** 04-29-2021

**Prepared by** Danica Fulmer

**Version #** 01

**Further information** CRC # 1750971

**Disclaimer** The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

**Revision information** This document has undergone significant changes and should be reviewed in its entirety.