



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3002 208-277V 1500W SPST Flush Mounting

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | 3002   |
| Manufacturer     | Nsi Industries   |
| Description      | Flush Mount, 208 to 277 V, 1500 W, 1 In Width, 2 In Height, Lexan Housing Material, SPST Switch Type, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Flush Mount, 0.1 LB/Ea |
| Weight per unit  | 0.1000 (lbs/each)  |
| Product Category | Lighting Photocells  |

### Features

|                |             |
|----------------|-------------|
| supply voltage | 208-277 VAC |
| Timing Range   | 2 Minutes   |

### Dimensions and Weight

|      |                  |
|------|------------------|
| Size | .375 Flush Mount |
|------|------------------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 208-277V 1500W SPST FLUSH MOUNTING  |
| extra long description | TORK 3002 Double Hook and Loop w/Ad |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Platinum Tools |
| GTIN  | 00786261600196 |
| UPC   | 786261600196   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
|----------------------|--|

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 12  |
| Weight Per each | 0.1 |

### Uses, Certifications, and Standards

|                          |                |
|--------------------------|----------------|
| Enclosure                | Lexan Housing  |
| environmental conditions | -40 to + 140 F |
| Frequency Rating         | 50-60 Hz       |
| Mounting                 | Flush Mount    |
| Operating Temperature    | -40 to + 140 F |