



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30090J In-Sure Push-In Wire Conn, 90 8-PRT BLCK, 100/Jar

Ideal

| | |
|------------------|-------------------------------------|
| Catalog Number | 30090J |
| Manufacturer | Ideal |
| Description | Ideal 30-090J Push-In 12AWG 8-Port, |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|---|
| connection | 8 Ports |
| Voltage Rating | 600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures |
| Wire Size | #12 AWG - #20 AWG Solid, #14 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand Or Less) Stranded, #12 AWG - #14 AWG (19 Strand Or Less) #16 AWG (26 Strand Or Less) 318 AWG (16 Strand Or Less) Stranded (Tin Bonded) |
| Wire Type | Solid, Stranded, Stranded (Tin Bonded) |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--|
| Size | 0.355 IN Length X 1.380 IN Width X 0.717 IN Height |
|------|--|

Descriptions

| | |
|------------------|--|
| Description | IN-SURE PUSH-IN WIRE CONN, 90 8-PRT BLCK, 100/JAR |
| Features | The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch circuit wiring application where a traditional twist-on wire connector would be used. Simply push the wire in – the low insertion force makes it easy. The color-coded shell allows for quick identification of port configuration while the clear polycarbonate housing allows for visual verification of every connection. The ergonomic design is easier to grip which me |
| Long Description | IDEAL 30-090J PUSH-IN 12AWG 8-PORT, |
| Product Type | Push-In 12AWG 8-Port, 100 Jar |
| Special Features | Features: No-Twist Connection Reduces Repetitive Motion Fatigue; Low Insertion Force For Fast And Easy Connections; Compact Size Makes Installation Easy; Clear Shell Gives Visual Verification Of Connection; UL Listed To 486C And CSA Certified To C22.2 #188; UL 467 Listed For Grounding And Bonding Applications; 600V Maximum Building Wire, 1000V; Maximum Signs And Lighting Fixtures; Shell Rated To 105 DEG C; Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F); Model: 90 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250460878 |
| Manufacturers Part Number | 30-090J |
| UPC | 783250460878 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type | Push-In |

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
| minimum qty | 100 |
| Status | Inactive |

Packaging

| | |
|-----------------|------|
| Carton | 100 |
| Package | 600 |
| Weight Per each | 1.46 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | For Grounding And Bonding Applications |
| standard | CSA C22.2 #188, 486C/467 UL Listed, RoHS |
| Temperature Rating | 105 DEG C Shell Rated |