



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street  
75482-0000, TX Sulphur Springs  
Phone: 903-885-0024  
Fax: 903-885-0352



## 301363 Weatherproof Wire Conn 63 Gray/DK Blue

*Ideal*

Catalog Number	301363
Manufacturer	Ideal
Description	Model 63 Gray-Blue 1000 BX
Weight per unit	17.9 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

Quantity	Box of 1000
----------	-------------

### Material, Color, and Finish

Color	Gray-Blue
-------	-----------

### Descriptions

Description	WEATHERPROOF WIRE CONN 63 GRAY/DK BLUE
extra long description	IDEAL 30-1363 WP MODEL 63 GRAY-BLUE
Features	100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsSwept wing design is built for comfort and efficiencyEliminates the need for heat-shrink or excessive tapingTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Models 61 and 63 approved for bonding and grounding applicationsFor use in damp/wet location or above-grade applications
Long Description	MODEL 63 GRAY-BLUE 1000 BX
Product Type	WP Model 63 Gray-Blue, 1000 BX
Special Features	Hexagonal shape allows connectors to be applied with standard nutdriver. Silicone-based sealant protects against moisture and corrosion. Easy to apply pre-filled twist-on wire connectors

### Manufacturer Information

Brand	Ideal
GTIN	00783250756384
Manufacturers Part Number	30-1363
UPC	783250756384

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Model 63® Connector

### Packaging

Carton	1000
Weight Per each	17.9



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street  
75482-0000, TX Sulphur Springs  
Phone: 903-885-0024  
Fax: 903-885-0352

## Uses, Certifications, and Standards

Application

Handles wire sizes from #16 to #6 AWG copper. Minimum of 3  
#14 AWG. Maximum of 2 #8 & 1 #10 AWG

standard

UL Listed to 486D for use with damp/wet locations