



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



260200086 2' 15A In Line Tri Cord *Southwire Company*

| | |
|------------------|--|
| Catalog Number | 260200086 |
| Manufacturer | Southwire Company |
| Description | 2FT 120V/15A In Line Tri Cord 12/3 Cable |
| Weight per unit | 1.0 (lbs/ft) |
| Product Category | 20120718074553 |

Features

| | |
|------------------|--------------|
| amperage rating | 15 |
| connection | NEMA |
| frame | in line |
| interrupt rating | 20 |
| Phase | 1 |
| Poles | 1 |
| trip range | 5 +/-1 mA |
| Trip Type | Ground Fault |
| Voltage Rating | 120 |

Descriptions

| | |
|------------------------|--|
| Description | 2' 15A IN LINE TRI CORD |
| extra long description | CLM 26020008-6 CORD SET, 12/3 2' 12 |
| Features | Yellow GFCI rated 12/3 SJTW Tri-Outlet Extension Cord with Lighted Tri-Source End. The Tri-Source End is molded T-head with three receptacles. Provides protection for the extra heavy duty cord and three attached tools used in outdoor/rugged jobsite environments. |
| Long Description | 2FT 120V/15A IN LINE TRI CORD 12/3 CABLE |
| Product Type | Cord Set, 12/3 2' 120V/15A Inline Tritap |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cables & Cords |
| GTIN | 00024098902145 |
| Manufacturers Part Number | 26020008-6 |
| UPC | 024098902145 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Portable Cords, Voice, Data, Video Wire & Cable |
| Type | Cord Set |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Package | 6 |
| Weight Per foot | 1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|------------------------|--------------------|
| Application | Construction |
| Frequency Rating | 50/60 Hz |
| standard | UL943 |