



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 270FSA 3/4" Alu Cond Body CVR Appleton/Oz Gedney

Catalog Number	270FSA
Manufacturer	Appleton/Oz Gedney
Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 3/4 In, Form: 7, Mounting: Screw-In, Material: Cast Aluminum, Finish: Epoxy Powder Coat, Standard: UI 514A, UI 514B, UI File Number E2527, Csa C22.2 No. 18.3, Csa 065183, Nema FB-1, For
Weight per unit	0.1500 (lbs/each)
Product Category	Alum

### Features

Form	7
------	---

### Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

### Dimensions and Weight

Hub Size	3/4
----------	-----

### Descriptions

Description	3/4" ALU COND BODY CVR
extra long description	APP 270FSA 3/4 FM7 COVER SAND-C
Long Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 3/4 IN, Form: 7, Mounting: Screw-In, Material: Cast Aluminum, Finish: Epoxy Powder Coat, Standard: UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1, For
Product Type	3/4 FM7 Cover Sand-Cast Al
Special Features	Approved for use in wet locations;Stainless steel screws;The cover is secured with clips, not screws;Unique Wedge-Lok clip cover design allows easy removal without damaging the conduit body;Wiring capacity: 0.8 CU-IN as per NEC 314.16(A)

### Manufacturer Information

Brand	Appleton
GTIN	00781381601276
Manufacturers Part Number	270FSA
UPC	781381601276

### Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Blank Clip Cover With Screw



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	50
Package	100
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	For FM7 Unilet Conduit Outlet Bodies
Mounting	Screw-In
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1